

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [18-12-2222](#)
Status: **Active**
Description: 3.18mm Diameter HCS-125 Pin and Socket Crimp Terminal, Series 2046, Male, with Tin (Sn) Plated Brass Contact, 16-18 AWG, Bag

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PSX-42179 \(PDF\)](#)

Agency Certification

CSA LR19980

General

Product Family Crimp Terminals
 Series [2046](#)
 Application Power
 Crimp Quality Equipment Yes
 MolexKits Yes
 Packaging Alternative [18-12-2221 \(Reel\)](#)
 Product Name HCS-125
 UPC 800753624917

Physical

Gender Male
 Material - Metal Brass
 Material - Plating Mating Tin
 Material - Plating Termination Tin
 Net Weight 0.500/g
 Packaging Type Bag
 Plating min - Mating 0.508µm
 Plating min - Termination 0.508µm
 Termination Interface: Style Crimp or Compression
 Wire Insulation Diameter 3.05mm max.
 Wire Size AWG 16, 18
 Wire Size mm² N/A

Material Info

Old Part Number 2046-1(P901)L

Reference - Drawing Numbers

Product Specification PSX-42179
 Sales Drawing SD-2046-1*




image - Reference only

EU RoHS

**ELV and RoHS
 Compliant**
**REACH SVHC
 Contains SVHC: No**
**Low-Halogen Status
 Low-Halogen**

China RoHS



**Need more information on product
 environmental compliance?**

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of
 Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
 non-product compliance questions.

Search Parts in this Series

[2046Series](#)

Mates With

[1901 Series](#), [2047 Series](#), [42555 Series](#)

Use With

[42179 Plug](#)

Application Tooling | [FAQ](#)

*Tooling specifications and manuals are
 found by selecting the products below.
 Crimp Height Specifications are then
 contained in the Application Tooling
 Specification document.*

Global

Description	Product #
Hand Crimp Tool	0638191100
Extractor Tool for .093 and HCS-125 Product Series	0638240200

This document was generated on 10/02/2014

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION