

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [19160-0012](#)
Status: **Active**
Overview: [Splices](#)
Description: Closed-End Insulated Splice for 14-22 AWG Wire, Clear

Documents:
[Drawing \(PDF\)](#) [Packaging Specification PK-19408-109 \(PDF\)](#)
[Product Specification PS-19902-013 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR18689
UL E32244

General

Product Family Splices
Series [19160](#)
Crimp Quality Equipment Yes
Mil-Spec N/A
MolexKits Yes
Overview [Splices](#)
Product Name Closed-End Insulated
UPC 800753110229

Physical

Barrel Type Closed
Color - Resin Natural
Flammability 94V-2
Insulation Nylon (PA)
Material - Metal Copper
Material - Plating Mating Tin
Material - Plating Termination Tin
Net Weight 0.472/g
Packaging Type Bag
Temperature Range - Operating 105°C
Wire Insulation Diameter 6.10mm max.
Wire Size AWG 14, 16, 18, 20, 22

Electrical

Voltage - Maximum 300V

Material Info

Old Part Number NC-2214

Reference - Drawing Numbers

[Packaging Specification](#) PK-19408-109
[Product Specification](#) PS-19902-013
[Sales Drawing](#) SD-19160-001




image - Reference only

Series

EU RoHS

**ELV and RoHS
Compliant**
REACH SVHC
Contains SVHC: No
Low-Halogen Status
Low-Halogen

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of
Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
non-product compliance questions.

Search Parts in this Series

[19160Series](#)

Application Tooling | FAQ

*Tooling specifications and manuals are
found by selecting the products below.
Crimp Height Specifications are then
contained in the Application Tooling
Specification document.*

Global

Description	Product #
Crimp Head for the AT-200™ Pneumatic Hand Tool, Crimp from Top	0640053400
Crimp Head for the AT-200™ Pneumatic Hand Tool	0640050600
Hand Crimp Tool	0640010600