


Multilayer Chip Varistor

MCVZ0402 Green Material Series



Description:

Multilayer Chip Varistor is a family of Transient Voltage Surge Suppression products. Today, electronic circuits are becoming smaller and more sensitive to external interference. Multilayer Chip Varistor is designed to protect components from destruction of transients and ESD(Electronic Static Discharge). The wide operating voltage and energy range make Multilayer Chip Varistor suitable for numerous applications on I/O protection , Vcc protection , Keyboard protection , LCD protection , Sensor protection etc. The Chip Varistor is manufactured by Multilayer fabrication technology providing excellent voltage clamping ability and is supplied in lead less , surface mount form , compatible with modern reflow and wave soldering procedures.

Features:

- Multilayer fabrication technology
- -55°C to +125°C operating temperature Range
- Operating voltage range $V_{M(DC)}$ at 5.5V to 18V
- Able to withstand ESD test of IEC-61000-4-2
- Bi-directional clamping characteristic

Applications:

Protection of cellular phones, PDA, High Speed Data Line etc.

ESD Protection for components sensitive to IEC 61000-4-2, provides circuit board transient voltage protection for transistors.

Protection of Video & Audio Ports.

Device Rating And Specifications:

Part Number	Maximum Ratings					Specifications		
	Max. Continuous Working Voltage		Max. Non-Repetitive Surge Current (8/20 μ s)	Max. Non- Repetitive Surge Energy (10/1000 μ s)	Max. Claiming Voltage at Specified Current (8/20 μ s)	Nominal Voltage At 1mA (DC) Current		Typical Capacitance
	$V_{M(DC)}$	$V_{M(AC)}$	I_{TM}	W_{TM}	Vc	$V_{N(DC)}$ Min.	$V_{N(DC)}$ Max.	@1KHz
	(V)	(V)	(A)	(J)	(V)	(V)	(V)	C
MCVZ0402M050AGT	5.5	4	20	0.05	20 at 1A	8.0	11.0	295
MCVZ0402M090AGT	9	6	20	0.05	23 at 1A	10.2	13.8	190
MCVZ0402M110AGT	11	8	20	0.05	25 at 1A	12.75	17.25	160
MCVZ0402M140AGT	14	11	20	0.05	30 at 1A	15.3	20.7	135
MCVZ0402M180AGT	18	14	20	0.05	40 at 1A	21.6	26.4	93

The capacitance value and energy only for reference. It is not formal specification.

Standard Testing Condition

Unless otherwise specified

Temperature : +15°C to 35°C
 Humidity : 25%RH to 85%RH
 Atmospheric pressure : 86kPa to 106kPa


www.element14.com
 www.farnell.com
 www.newark.com



Multilayer Chip Varistor

MCVZ0402 Green Material Series

Dimensions:



Symbol	MCVZ0402 Series
L	1 ±0.1mm
W	0.5 ± 0.1mm
T	0.6mm (max.)
Ts	0.25 ±0.15mm

Terminal electrode : Ni / Sn electrode

Specifications:

Electrical Reliability

Test Item	Test condition / Test method	Specification															
High temperature storage	+125±3°C for 1,000 hours Measurement to be made after keeping at room temp. for 24 ±2hr	ΔV at 1mA < 10%															
Low temperature storage	-40±3°C for 1,000 hours Measurement to be made after keeping at room temp. for 24 ±2hr	ΔV at 1mA < 10%															
Humidity storage	40±2°C , 90 to 95%RH for 500 hours Measurement to be made after keeping at room temp. for 24 ±2hr	ΔV at 1mA < 10%															
Temperature cycles	Times : 5 cycles <table border="1"> <thead> <tr> <th>Step</th> <th>Temp.(°C)</th> <th>Time(min.)</th> </tr> </thead> <tbody> <tr> <td>1</td> <td>-55±3</td> <td>30±3</td> </tr> <tr> <td>2</td> <td>Room temp.</td> <td>2~3</td> </tr> <tr> <td>3</td> <td>+125 ±3°C</td> <td>30±2</td> </tr> <tr> <td>4</td> <td>Room temp.</td> <td>2~3</td> </tr> </tbody> </table> Measurement to be made after keeping at room temp. for 24 ±2hr	Step	Temp.(°C)	Time(min.)	1	-55±3	30±3	2	Room temp.	2~3	3	+125 ±3°C	30±2	4	Room temp.	2~3	ΔV at 1mA < 10%
Step	Temp.(°C)	Time(min.)															
1	-55±3	30±3															
2	Room temp.	2~3															
3	+125 ±3°C	30±2															
4	Room temp.	2~3															


Mechanical Reliability

Test Item	Test condition / Test method	Specification
Solderability	Solder temp. : 230±5°C Immersion time : 2±0.5 sec Immersion and emersion rates : 25mm/s	Min 90% electrode shall be covered with solder.
Resistance to Soldering Heat	Pre-heating : 120°C to 150°C, 60sec Solder temp. : 260 ±5°C Immersion time : 10 ±1sec Measurement to be made after keeping at room temp. for 24 ±2h	ΔV at 1mA < 10% Disappearance of electrode due to immersion into solder shall not exceed 25% of edges of each electrode.

Multilayer Chip Varistor


MCVZ0402 Green Material Series

Mechanical Reliability

Test Item	Test condition / Test method	Specification
Adhesive Strength of Termination	<p>Solder chip on PCB and applied 0805/1206 Series: 10N(1Kgf) for 10 sec 0402/0603 Series: 5N(0.5Kgf) for 10 sec</p> <p style="text-align: center;">Chip varistor</p> 	No visible damage
Vibration	<p>Solder chip on PCB. Frequency : 10Hz ~ 55Hz ~ 10 Hz (1min) Oscillation amplitude : 1.5mm Times : 2hrs in each of three perpendicular direction</p>	No visible damage
Bending Test	The middle part of substrate shall be pressurized by means of the pressurizing rod at a rate of 1mm per second until the deflection becomes 1mm and then the pressure shall be maintained for 5 sec.	No visible damage ΔV at 1mA < 10%

Soldering Condition:

Typical examples of soldering processes that provide reliable joints without any damage are given in figure below:



Infrared soldering profile


Multilayer Chip Varistor

MCVZ0402 Green Material Series



Packaging:

Paper Tape specifications and Packaging quantity




Series	A	B	E	F	ØD
MCVZ0402 Series	1.12 ±0.03	0.62 ±0.03	1.75 ±0.05	3.5 ±0.05	1.55 ±0.05

Series	P0	P1	T	W	Quantity/Reel
MCVZ0402 Series	4 ±0.1	2 ±0.1	0.6 ±0.03	8 ±0.2	10Kpcs

Tape Material : Paper tape

Dimensions : Millimetres

Reel Dimensions:



Index	A	B	C
Dimension (mm)	178	60	13.5

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of the Group. © Premier Farnell plc 2012.

www.element14.com
 www.farnell.com
 www.newark.com

