# **Features**

## **Unregulated** Converters

- Twin Independent Outputs
- Output/Output Isolation 1kVDC
- Power Sharing on Outputs
- Input/Output Isolation 1kVDC
- Standard and Miniature Versions
- **Optional Continuous Short Circuit Protected**
- **Custom Solutions Available**
- Efficiency to 76%

#### Description

The RU DC/DC converter offers two independent isolated outputs. Typical applications include multiple channel circuits where inter-channel isolation is also required. The RUM offers similar specifications in a miniature case for applications where space is

at a premium. Both converters offer 1KVDC input/output isolation and 1kVDC output/output isolation. The /H versions offer 2kVDC isolation between input and outputs.

### **Selection Guide**

Input Voltage Range

Part Number SIP 7	2kV	Input Voltage (VDC)	Output Voltage (V1VDC)	Output Voltage (V2VDC)	Output Current (mA)	Efficiency typ. (%)	Max Capacitive Load <sup>(1)</sup>
RU-3.30505	(H)	3.3	5	5	100/100	76	470μF/470μF
RU-050505	(H)	5	5	5	100/100	72	470μF/470μF
RUM-3.30505	(H)	3.3	5	5	100/100	78	470μF/470μF
RUM-050505	(H)	5	5	5	100/100	72	470μF/470μF

Other input and output voltage combinations available on request

#### **Specifications** (measured at $T_A = 25$ °C, nominal input voltage, full load and after warm-up)

Output Voltage Acc	curacy		±5%		
Line Voltage Regu	lation		1.2%/1% of Vin typ.		
Load Voltage Regu	ılation		15% max		
(10%~100% Load	d)		10% typ.		
Output Ripple and	Noise (20MHz limited)	RU	75mVp-p max.		
Full Load		RUM	100mVp-p max.		
Operating Frequer	псу	20kHz min. / 70kHz typ. / 105kHz max.			
Efficiency at Full L	oad	RU	70% min.		
		RUM	70% min.		
Minimum Load =	0%	Specifications valid for	Specifications valid for 10% minimum load only.		
Isolation Voltage		(tested for 1 second)	1000VDC		
Input/Output and 0	Output/Output	(rated for 1 minute**)	500VAC / 60Hz		
Isolation Voltage	H-suffix	(tested for 1 second)	2000VDC		
Input/Output	H-suffix	(rated for 1 minute**)	1000VAC / 60Hz		
Output/Output	H-suffix	(rated for 1 minute**)	500VAC / 60Hz		
solation Capacitance 20pF min. / 94pF ma					
Isolation Resistance 10 G $\Omega$ r					
Short Circuit Protection 1 Second					
P-Suffix			Continuous		
Operating Temperature Range (free air convection) -40°C to +85°C (see Gra					
Storage Temperati	ure Range		-55°C to +125°C		
Relative Humidity			95% RH		
Package Weight			2.7g		
Packing Quantity		RU	25 pcs per Tube		
		RUM	30 pcs per Tube		
MTBF (+25°C) \	Detailed Information see	using MIL-HDBK 217F	1012 x 10 <sup>3</sup> hours		
(+85°C) ∫	Application Notes chapter "N	ATBF" using MIL-HDBK 217F	151 x 10 <sup>3</sup> hours		
Certifications					

EN60950-1 Report: SPCLVD1109103 EN60950-1: 2006+A12:2011

## **ECONOLINE**

DC/DC-Converter with 3 year Warranty



# 1 Watt SIP7 **Isolated Dual Output**





±10%




EN-60950-1 Certified

# **RU/RUM**

# **Derating-Graph**

(Ambient Temperature)



<sup>\*\*</sup>Any data referred to in this datasheet are of indivative nature and based on our practical experience only. For further details, please refer to our Application Notes.

**Refer to Application Notes** 


<sup>\*</sup> add Suffix "P" for Continuous Short Circuit Protection,


e.g. RU-050505/P, RUM-050505/P, RU-3.30505/HP

# RU/RUM Series

#### **Typical Characteristics**

#### RU-050505 RUM-050505






Notes

Note 1

Maximum capacitive load is defined as the capacitive load that will allow start up in under 1 second without damage to the converter.

#### **RU Package Style and Pinning (mm)**


#### SIP7 Package








#### **Recommended Footprint Details**






#### Pin Connections

Pin#	Single	
1	+Vin	
2	–Vin	
4	+Vout 1	
5	–Vout 1	
6	+Vout 2	XX.X ± 0.5 mm
7	-Vout 2	XX.XX ± 0.25 mi

#### **RUM Package Style and Pinning (mm)**


#### SIP6 Package








#### **Recommended Footprint Details**








Pin #	Single		
1	+Vin		
2	–Vin		
3	-Vout 1		
4	+Vout 1		
5	-Vout 2		
6	+Vout 2		

 $XX.X \pm 0.5 \text{ mm}$  $XX.XX \pm 0.25 \text{ mn}$ 

#### **Typical Application**



The product information and specifications are subject to change without prior notice. All products are designed for non-safety critical commercial and industrial applications.

The Buyer agrees to implement safeguards that anticipate the consequences of any failures that might cause harm, loss of life and/or damage property.