



E25100

iQ Magnifier LED Lamp with its modern, sleek ergonomic design has a large 1.75x crystal clear lens and 60 ultra bright daylight LED's for accurate viewing of details.

Perfect for all industrial purposes, clinics, laboratories, beauty salons and for the visually impaired.

It has a flexible joint between the head and spring balanced arm, this gives effortless movement and long reach with accurate positioning and no drift.

iQ has 60 LED's which have a life expectancy of up to 20,000 hours or over 20 years use. No bulb or tube to replace.



60 LEDs



90% less
energy



FreeMotion™
Head-joint



Metal table
clamp



Powerful 7"
magnifier



Overview

- 60 daylight premium LED's
- 4 stepped dimmer
- 17.5cm (7") lightweight lens with anti-scratch coating
- Quick swap lens system - 5D & 12D optional lenses available separately
- Effortless free-motion movement head and arm. Hold any position without drift
- Reinforced heavy duty arm with sealed joints, solid pivots and side covers
- Long reach 118cm (46.5") max
- LED's never need replacing
- Lux at 15cm 6,330 max



Technical information

Packaging information	
Item code	E25100
Colour box width	605mm (23.82 in)
Colour box depth	100mm (3.94 in)
Colour box height	460mm (18.11 in)
Total packed weight	4.6kg (10 lbs)
Products per carton	2
Product information	
Assembled Width	23.0cm (9 in)
Assembled Height	57.0cm (22½ in)
Assembled Depth	90.0cm (35½ in)
Assembled Weight	3.8kg (8½ lbs)
Length of cable	2.5m
Main colour	Grey/White
Light output information	
Light source type	LED
Total wattage	12.0w
Colour temperature	6,000 - 6,500K
Magnifier info	
Main lens size	17.5cm (7 in)
Main lens magnification	1.75x

Contact us

The Daylight Company Ltd
Info.uk@daylightcompany.com
UK + 44 (0)20 8964 1200
FR 0825 00 49 46
DE 0800 329 2667



MULTI ANGLE HOBBY VICE (1-83-069)



Features and Benefits:

- The patented ball joint allows you to rotate your project a full 360 degrees and lock it at any angle
- Multiple positions for convenience and easier access
- 3" jaw opening holds a wide range of items
- Removable rubber jaw covers wide range of applications for protecting delicate finishes
- The large C-clamp mount attaches to work surfaces up to 2 3/8" thick - also suitable for heavy duty applications
- Wide range of applications
- Lightweight and very strong
- Protects delicate finishes

Target Users: Technicians, Electricians, Mechanics, Hobbyists, and DIY'ers

Applications: Traditional vice applications, assembly works, arts & crafts, electronics and model building

2409381 + 1696668 = **BUNDLE (MFR PART NUMBER 24490580)**