



CAT5e Snagless Patch Cable * RJ45M/RJ45M; 10 White

A3L791-10-WHT-S



Belkin CAT5e Networking Cables allow you to connect your IT hardware to the network, providing reliable performance.

FEATURES:

- CAT 5e UTP Stranded Cable: PVC
- Standards Compliance: ISO/IEC 11801; TIA/EIA-568-B.2
- Conductor Size: 24AWG x 4pairs
- Conductor Construction: Bare Stranded Copper
- Insulation Material: HDPE
- Jacket Diameter: 5.5±0.15mm
- Jacket Material: PVC
- Rating: 75°C, 300V
- Conductor Resistance: 89.2Ω/km/20°C max
- Mutual Capacitance: 56pF/m max
- Dielectric Strength: AC 1.75kV/0.15sec
- Spark Test: AC 1.75kV/0.15sec
- Flame Retardant Test: CM
- Characteristic Impedance: 100±15Ω @ 1 ~ 100MHz
- Structural Return Loss: 19.0dB min at 100MHz
- Propagation Delay: 538nS/100m max @ 100MHz
- Category 5e performance rated for any 10Base-T and 100Base-T Networks
- PowerSum tested
- Premium snagless-type moldings to protect the connection

SPECIFICATIONS:

General

- Network Cable Type: Patch cable - CAT 5e
- Features: Molded, snagless , gold plated connectors
- Length: 10 ft
- Color: White

Connectivity

- Connector(s): 1 x RJ-45 - male
- Connector(s) (Other Side): 1 x RJ-45 - male

Miscellaneous

- Manufacturer Selling Program: Belkin B2B

Manufacturer Warranty

- Service & Support: Limited lifetime warranty

Compatibility Information

- Designed For: Belkin Omniview SMB 1x16 KVM-over-IP Switch, SMB 1x8 KVM-over-IP Switch, Belkin OmniView SMB CAT5 KVM Switch