32.768 kHz LOW FREQUENCY SMD CRYSTAL

ABS25

Pb in High Tempe rature Solder (exempt per RoHS 2002/95/EC Annex (7))





FEATURES:

- Plastic molded SMD
- 2.5mm height ideal for high density circuit boards
- Suitable for RoHS compliant reflow
- Extended temperature -40°C to +85°C for industrial applications

> APPLICATIONS:


- Wide range in communication & measuring equipment
- Commercial & Industrial applications
- Computer clock

STANDARD SPECIFICATIONS:

Parameters	Minimum	Typical	Maximum	Units	Notes
Nominal Frequency		32.768		kHz	
Frequency Range	30		100	kHz	
Operating Temperature	-40		+85	°C	
Turnover Temperature	+20	+25	+30	°C	
Storage Temperature	-55		+125	°C	
Frequency Tolerance @+25°C	-20		+20	ppm	32.768kHz
	-30		+30		Other frequencies See options
Capacitance Ratio (C0/C1)		450			32.768kHz
		425 to 800			Other frequencies
Frequency Coefficient (B)	-0.040	-0.034	-0.028	ppm/T ²	
Equivalent series resistance (R1)			50	kΩ	
Shunt capacitance (C0)		1.35		pF	32.768kHz
		0.8 to 1.7		pF	Other frequencies
Load capacitance (CL)		12.5		pF	See options
Drive Level			1	μW	
Aging	-3		+3	ppm	@25°C±3°C
	-5		+5		First year
Insulation Resistance	500			MΩ	@ $100 \text{Vdc} \pm 15 \text{V}$

> OPTIONS AND PART IDENTIFICATION:

(Left blank if standard)



^{*}STD for 32.768kHz. Please leave this blank if F is 32.768kHz.





^{**}STD for other frequencies. Please leave this blank if F is not 32.768kHz.

32.768 kHz LOW FREQUENCY SMD CRYSTAL


ABS25

Pb in High Tempe rature Solder (exempt per RoHS 2002/95/EC Annex (7)) Compliant






OUTLINE DRAWING:




0.315Max


(8.0)

0.22 Ref (5.5)



Electrade Arrangement Pin 2 and 3 are not connected to the GND (Floating)







Dimensions: (inches) mm

► TAPE & REEL:

(0.5)



REFLOW PROFILE



ATTENTION: Abracon Corporation's products are COTS – Commercial-Off-The-Shelf products; suitable for Commercial, Industrial and, where designated, Automotive Applications. Abracon's products are not specifically designed for Military, Aviation, Aerospace, Life-dependant Medical applications or any application requiring high reliability where component failure could result in loss of life and/or property. For applications requiring high reliability and/or presenting an extreme operating environment, written consent and authorization from Abracon Corporation is required. Please contact Abracon Corporation for more information.



