


Siemens Matsushita Components



Ferrites and Accessories


RM Coil Formers for Power Applications

Data Book Supplement

Optimized for automatic winding

For matching clamp and insulating washer 1 see data book, page 221


| Sections | A _N mm ² | / _N mm | A _R value μΩ | Pins | Ordering code | PU Pcs |
|----------|-----------------------------------|----------------------|----------------------------|------|-----------------|-----------|
| 1 | 15 | 30 | 69 | 8 | B65808-E1508-T1 | 500 |



Optimized for automatic winding

For matching clamp and insulating washer 1 see data book, page 252

| Sections | A _N mm ² | / _N mm | A _R value μΩ | Pins | Ordering code | PU Pcs |
|----------|-----------------------------------|----------------------|----------------------------|------|-----------------|-----------|
| 1 | 30 | 42 | 47 | 12 | B65812-C1512-T1 | 200 |




Hole arrangement View in mounting direction (Note half pitch!)


Optimized for automatic winding


Material:GFR polyterephthalate (UL 94 V-0, insulation class to IEC 85:
F \triangleq max. operating temperature 155 °C), color code blackSolderability:to IEC 68-2-20, test Ta, method 1 (aging 3): 235 °C, 2 sResistance to soldering heat:to IEC 68-2-20, test Tb, method 1B: 350 °C, 3,5 sWinding:see data book 1994 "Ferrites and Accessories", page 150

For matching clamp and insulating washer 1 see data book, page 265

| Sections | A _N mm ² | / _N mm | A _R value μΩ | Pins | Ordering code | PU Pcs |
|----------|-----------------------------------|----------------------|----------------------------|------|-----------------|-----------|
| 1 | 41,5 | 52 | 43 | 12 | B65814-C1512-T1 | 200 |








Hole arrangement View in mounting direction (Note half pitch!)

For matching clamp see data book, page 277

| Sections | A _N mm ² | / _N mm | A _R value μΩ | Pins | Ordering code | PU Pcs |
|----------|-----------------------------------|----------------------|----------------------------|------|-----------------|-----------|
| 1 | 72 | 61 | 28,7 | 12 | B65816-C1512-T1 | 100 |




Hole arrangement View in mounting direction (Note half pitch!)

5.96

For matching clamp see data book, page 285

| Sections | A _N mm ² | / _N mm | A _R value μΩ | Pins | Ordering code | PU Pcs |
|----------|-----------------------------------|----------------------|----------------------------|------|-----------------|-----------|
| 1 | 106 | 71,5 | 23 | 12 | B65888-C1512-T1 | 100 |



Published by Siemens Matsushita Components GmbH & Co. KG Marketing Kommunikation, Postfach 80 17 09, D-81617 München

© Siemens Matsushita Components 1996. All Rights Reserved.

As far as patents or other rights of third parties are concerned, liability is only assumed for components per se, not for applications, processes and circuits implemented within components or assemblies.

The information describes the type of component and shall not be considered as assured characteristics.

Terms of delivery and rights to change design reserved.

This brochure replaces the previous edition.

For questions on technology, prices and delivery please contact the Sales Offices of Siemens AG, Passive Components and Electron Tubes Group, in the Federal Republic of Germany or the international Siemens Companies and Representatives.

Due to technical requirements components may contain dangerous substances. For information on the type in question please also contact one of our Sales Offices.