



- **Black Box Products**

## Cables > Computer & Data Cables

click photo to enlarge

### IEEE 488 Cable, Double-Headed Male/Female, Both Ends, 4-m (13.1-ft.), (HP Part #9644M)

Shielded 488 cable that's 100% compatible with your shop or lab systems.

EXN04M

Extended Double Diamond™ Warranty Available (Lifetime)

#### **Product Highlights**

- Ideal for use with expansion cards in PCs, switches, buffers, and other peripherals when space is tight.
- PVC insulation gives your cable flexibility and a longer life.
- Male and female contacts prevent cable mismatches and enable daisy chaining.
- Guaranteed for life!



- [Details](#)
- [Warranty](#)
- [Similar Products](#)

#### **Description**

IEEE 488 Cable, Double-Headed Male/Female, Both Ends, 4-m (13.1-ft.)

#### **Quick Facts**

- Ideal for use with expansion cards in PCs, switches, buffers, and other peripherals when space is tight.
- PVC insulation gives your cable flexibility and a longer life.
- Male and female contacts prevent cable mismatches and enable daisy chaining.
- Guaranteed for life!

#### **Further Details**

- Choose straight-in or right-angle connectors to solve the problem of tight PC/peripheral connections. Our IEEE 488 cables are compatible with all devices that have the standard IEEE 488 interface. You can interconnect up to 15 programmable instruments in star or daisy chain networks.

These cables are virtually impervious to damage from mishandling. Fully molded construction features nickel-plated connector shells and gold over nickel-plated beryllium copper contact pins to withstand make/break cycling.

PVC insulation protects conductors from flexing damage, and durable tinned copper-braid shields help guard against electrical interference.

The right-angle connectors have both male and female contacts to prevent cable mismatches and to enable daisy chaining. For tight spaces, choose our cable with one right-angle double connector and one straight-in male connector.