

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

74441-0010

Status:

Active

Overview:

XFP Products

Description:

0.80mm Pitch SFP, SFP Plus (SFP+) Host Connector, Z-Axis Pluggable, Right Angle, Surface Mount, 20 Circuits, 0.76µm Gold (Au)



Series
image - Reference only

- Documents:
- 3D Model

Drawing (PDF)

Product Specification PS-74441-001 (PDF)

Application Specification AS-74441-001 (PDF)

Test Summary TS-74441-0003 (PDF)

Test Summary TS-74441-002 (PDF)

Test Summary TS-74441-010 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

CSA

LR19980

UL

E29179

General

Product Family

I/O Connectors

Series

74441

Application

Module-to-Board

Component Type

Receptacle

Electrical Model

Yes

Overview

XFP Products

Product Name

SFP, SFP Plus

Type

N/A

UPC

800756382647

Physical

Boot Color

N/A

Circuits (Loaded)

20

Circuits (maximum)

20

Circuits Detail

20

Color - Resin

Black

Durability (mating cycles max)

200

Flammability

94V-0

Gender

Receptacle

Keying to Mating Part

Yes

Lock to Mating Part

Yes

Material - Metal

High Performance Alloy (HPA)

Material - Plating Mating

Gold

Material - Plating Termination

Tin

Material - Resin

High Temperature Thermoplastic

Net Weight

0.700/g

Number of Rows

2

Orientation

Right Angle

PCB Locator

Yes

PCB Retention

Yes

Packaging Type

Embossed Tape on Reel

Panel Mount

No

Pitch - Mating Interface

0.80mm

Pitch - Termination Interface

0.80mm

Plating min - Mating

0.762µm

Plating min - Termination

2.540µm

Polarized to Mating Part

Yes

Polarized to PCB

No

Ports

1

EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Contains SVHC: No

Low-Halogen Status

Low-Halogen

China RoHS

Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
74441Series

Mates With
SFP Modules

Use With
EMI Shield, 73927 SFP Cage, 86025 LC Duplex Cable Assembly, Guide Frame, 73939 HSSDC2 Cable Assembly

Surface Mount Compatible (SMC)	Yes
Temperature Range - Operating	-40°C to +85°C
Termination Interface: Style	Surface Mount
Waterproof / Dustproof	No
Wire Size AWG	N/A

Electrical

Current - Maximum per Contact	0.5A
Grounding to Panel	Yes
Shielded	No
Voltage - Maximum	30V AC (RMS)/DC

Solder Process Data

Duration at Max. Process Temperature (seconds)	40
Lead-free Process Capability	Reflow Capable (SMT only)
Max. Cycles at Max. Process Temperature	3
Process Temperature max. C	260

Material Info

Reference - Drawing Numbers

Application Specification	AS-74441-001
Electrical Model Document	EE-74441-001
Product Specification	PS-74441-001
S-Parameter Model	SP-74441-001
Sales Drawing	SD-74441-001
Test Summary	TS-74441-0003, TS-74441-002, TS-74441-010

This document was generated on 10/13/2014

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION