

# Waveform Generator DDS/ARB



## Features:

Channels	2
Sample Rate	250MS/S
Output Frequency	60MHz
Frequency Resolution	1µHz
Vertical Resolution	14bits
Max. Arb Memory Depth	1Mpts
Waveforms	Sine, Square, Ramp, Triangle, Pulse, Noise, DC, Arb
Output Amplitude Range	1mVpp to 10Vpp (50Ω), 2mVpp to 20Vpp (1MΩ)
Modulation Types	AM, FM, PM, ASK, FSK, PWM, SWEEP, BURST
Interfaces	USB DEVICE, USB Host, LAN

## General Characteristics:

Power	100-240V AC / 40-400Hz
Product Colour	White and Grey
Product Net Weight	3.2kgs
Product Size	231mm × 94mm × 283mm
Standard Accessories	BNC to BNC Cable, Power Cord, USB CABLE, PC SOFTWARE CD
Standard Individual Packing	1pc Gift Box, English Manual

## Part Number Table

Description	Part Number
Waveform Generator; DDS/ARB	72-2500

**Important Notice :** This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Tenma is the registered trademark of the Group. © Premier Farnell plc 2012.

