

Model 405

Electronic Bench Scale



- Portable
- Large stainless steel top
- Simple to use
- Capacity 6 kg and 15 kg
- Large red LED display
- Mains or battery powered

Model 405 Electronic Bench Scale

Features

Model 405 electronic bench scale is a totally portable machine ideal for use in a wide range of applications where high accuracy weighing is required.

With a choice of 6 kg x 1 g or 15 kg x 2 g capacities, the 405 is a self-contained unit powered by an internal rechargeable battery – with a massive 160 hours between recharges. Alternatively the machine can be powered direct from mains via the 12 volt AC adaptor included.

Featuring a large stainless steel platform - 245 mm x 215 mm and housed in a tough ABS case mounted on four adjustable feet, the model 405 is targeted at applications such as catering kitchens, post rooms, stores areas, warehouses and any other area where weighing needs to be carried out away from mains power. A level bubble is built in.

The model 405 display is easy to read, even in poorly lit areas and has large 17 mm high, red LED display digits. The display also includes annunciators for zero, net, AC mains connected, recharge battery, kg, lb, g and oz.

Simple two button front panel – on/off/zero and tare/units. Tare allows for the weight of containers to be removed and the net weight only displayed.

Units switches the machine between kg, lb, gram and ounce display.

The scale features auto-zero tracking to automatically compensate for small fluctuations in zero, such as a build-up of material on the platform.

To extend battery life, an auto-off feature is standard. The operator can set the auto-off timing to between one minute and nine minutes of inactivity to suit the application. Alternatively the auto-off function can be switched off, leaving the scale permanently on until switched off by the operator.

Capacity -

6 kg x 1 g/12 lb x 0.002 lb

Specifications

15 kg x 2 g/30 lb x 0.005 lb

Power - Internal rechargeable battery giving 160 hours of use between charges.

Recharge time approximately 8 hours.

12 volt UK/EU power adaptor/recharger (supplied)

Auto-off - Selectable between 1 and 9 minutes or off

Platform Size - 245 mm x 215 mm

Platform Material - Stainless steel

Case size overall - 250 mm wide x 300 mm long x 95 mm high

Level bubble built in, four levelling feet

Display - 7 digit, 17 mm high, red LED

Function Keys - On/off/zero; tare/units

Annunciators - Zero; net; AC mains connected; recharge battery; kg; lb; gram and oz

Tare - 100% subtractive

Operating Temperature - 0° C to + 40° C

Approvals - CE
WEEE directive

Unit Weight - 2.8 kg

Packing Dimensions - 370 mm x 325 mm x 200 mm

Packed Weight - 4.2 kg

Product Code -

6 kg x 1 g/12 lb x 0.002 lb - 816965002146

15 kg x 2 g/30lb x 0.005 lb - 816965002153



a division of Avery Weigh-Tronix

Salter Brecknell Weighing Products

P.O. Box 9533, Smethwick, West Midlands, B66 2TE

Tel: 0870 444 6132 Fax: 0870 010 2241

E-mail: sales@salterbrecknell.co.uk

www.salterbrecknell.co.uk

