



Einhell

CLASSIC

GH-BC 43 AS

Petrol

Features

- High quality 2-stroke engine (1)
- Twin handle including all operational functions (2)
- Tool-free and universal adjustable twin handle (Bike handle) made of aluminium for easy and accurate guidance (3)
- Aluminium shaft for fatigue-free working (4)
- Split shaft for easy transport and space saving storage (5)
- Knife protection cover (6)
- 3-teeth blade (7)
- Twin line spool with automatic jog system (8)
- Comfort carrying belt (9)
- Quick Start System: well reachable primer (10) (manual fuel pump) and auto choke for quick and easy starting
- Anti-vibration function
- Full crank shaft
- Centrifugal clutch for cutting attachment

Technical Data

- Power: **1.25 kW (1.7 HP)**
- Engine: 2-stroke
- Capacity: 42.7 ccm
- Cutting width double line: 42 cm
- Thread length: 4 m
- Thread-Ø: 2.4 mm
- Cutting width knife: 25.5 cm
- Petrol tank volume: 1 l
- Product weight: 8.9 kg

Logistic Data

- Net weight: 9.1 kg
- Gross weight: 10.3 kg
- Packing dimensions: 990 x 330 x 315 mm
- Bar code: 4006825582543
- Sales unit: 1 pc

Passes the pollutants directive 2002/88 EC (emission 2)

