

# AN-1940 LMP8601 Evaluation Board

### 1 Introduction

The LMP8601 current sense evaluation board is designed to evaluate the LMP8601, 60 V common mode, bidirectional precision current sensing amplifier. This board has a LMP8601 part mounted on the printed circuit board (PCB) together with the required de-coupling capacitor, power supply connections, input and output (I/O) connectors and a 3-pin header for connecting the offset pin to either GND or  $V_s$ .




Figure 1. The LMP8601 Evaluation Board

## 2 General Description

The LMP8601 and LMP8601Q are fixed 20x gain precision amplifiers. The part amplifies and filters small differential signals in the presence of high common mode voltages. The input common mode voltage range is -22 V to +60 V when operating from a single 5 V supply. With 3.3 V supply, the input common mode voltage range is from -4 V to +27 V. The LMP8601 and LMP8601Q are members of the Linear Monolitic Precision (LMP<sup>TM</sup>) family and are ideal parts for unidirectional and bidirectional current sensing applications. All parameter values of the parts that are shown in the tables of the *LMP8601*, *LMP8601-Q1* 60-V Common-Mode Bidirectional Precision Current Sensing Amplifier Data Sheet (SNOSAR2) are 100% tested and all bold values are also 100% tested over temperature.

LMP is a trademark of Texas Instruments. All other trademarks are the property of their respective owners.



#### LMP8601 Operating Conditions

www.ti.com

The part has a precise gain of 20x, which is adequate in most targeted applications to drive an ADC to its full scale value. The fixed gain is achieved in two separate stages, a pre-amplifier with a gain of 10x and an output stage buffer amplifier with a gain of 2x. The connection between the two stages of the signal path is brought out on two pins to enable the possibility to create an additional filter network around the output buffer amplifier. These pins can also be used for alternative configurations with different gain as described in the *Applications Information* section of the *LMP8601*, *LMP8601-Q1 60-V Common-Mode Bidirectional Precision Current Sensing Amplifier Data Sheet* (SNOSAR2).

The mid-rail offset adjustment pin enables you to use these devices for bidirectional single supply voltage current sensing. The output signal is bidirectional and mid-rail referenced when this pin is connected to the positive supply rail. With the offset pin connected to ground, the output signal is unidirectional and ground-referenced.

The LMP8601Q incorporates enhanced manufacturing and support processes for the automotive market, including defect detection methodologies. Reliability qualification is compliant with the requirements and temperature grades defined in the AEC Q100 standard.

#### 3 LMP8601 Operating Conditions

- Temperature Range -40°C to 125°C
- Power Supply Voltage 3.0 V  $\leq$  V<sub>s</sub>  $\leq$  5.5 V
- CMVR at  $V_s = 3.3 \text{ V} 4 \text{ V}$  to 27 V
- CMVR at  $V_s = 5.0 \text{ V} 22 \text{ V}$  to 60 V

### 4 Description of the LMP8601 Evaluation Board

The LMP8601 evaluation board requires a power supply with a voltage between 3.0 V and 5.5 V, the supply current will be <2 mA in normal operation with high-impedance load on the output of the part. The positive supply voltage is connected to  $V_s$  (P5). The negative supply voltage is connected to GND (P6).

The offset voltage on the output of the LMP8601 is determined by the voltage on the offset pin, which is connected to pin2 of J1 and the offset voltage will be  $V_{Offset}/2$ . This pin is normally connected with a jumper to GND or  $V_S$ , but this pin can also be driven from a low impedance source (<10  $\Omega$ ).

With a jumper on J1 between 1–2, the offset pin is connected to  $V_s$  and the offset voltage is half the value of  $V_s$ . In this configuration, the LMP8601 can be used for measuring bidirectional currents.

With a jumper on J1 between 2–3, the offset pin is connected to GND and the output voltage is ground referenced. In this configuration, the LMP8601 is used for measuring unidirectional currents.

The input signal is connected between +IN (P1) and -IN (P2) and the output signal is available at OUT (P3).

On the board there is the possibility to place a capacitor C2 that creates a low-pass filter between the first and second stage. This can be used to reduce the output noise and glitches that might appear from switching large common mode voltages with very fast transients at the input. (For more details about this filter, see the *Application Information* section of the *LMP8601*, *LMP8601*-Q1 60-V Common-Mode Bidirectional Precision Current Sensing Amplifier Data Sheet (SNOSAR2).

The Header J2 is normally shorted with a jumper and connects the first stage to the second stage. The *Application Information* section of the *LMP8601*, *LMP8601-Q1 60-V Common-Mode Bidirectional Precision Current Sensing Amplifier Data Sheet* (SNOSAR2) explains more about the alternative configurations that can be made after removing the jumper on J2.






Figure 2. Power Supply Connectors and Headers

#### 5 PCB Layout Guidelines

This section provides general practical guidelines for PCB layouts that use various power and ground traces. Designers should note that these are only "rule-of-thumb" recommendations and the actual results are predicated on the final layout.

#### 5.1 Differential Signals

The two input pins of the LMP8601 form a differential pair that must be handled following the rules given below.

- Keep both signals coupled by routing them closely together and keeping them of equal length.
- Do not allow any other signal in between these two signals of the differential pair.
- Keep all impedances in both traces of the signal equal.

#### 5.2 Power, Ground and De-Coupling

Keep the power supply de-coupling capacitor close to the power supply pin (V<sub>s</sub> of the part.)

Make sure all return currents of the signals can flow next to the originating signals

## 6 Description of Headers and Connectors of the LMP8601 Evaluation Board

The LMP8601 evaluation board provides the following headers and connectors for connecting test equipment and supplying the LMP8601 part.



#### Connector and Header Functions

### 7 Connector and Header Functions


Designator	Function or Use	Comment
J1	Offset selection	1–2 Mid rail offset (Bi-directional)2–3 Ground Referenced (unidirectional)
J2 the second stage	Short to connect first stager output to output amplifier input	Normally shorted
P1	Positive Input	
P2	Negative Input	
P3	Output	
P5	supply V <sub>s</sub>	
P6	ground connection (GND)	

# 8 Bill of Materials (BOM)

Designator	Component	Value	Tolerance	Comment	Package Type
C1	Capacitor	100 nF			0603
C2	Capacitor	N/A			0603
J1	Header 2 pin			Mid-rail Offset	
J2	Header 2 pin				
P1	Banana plug	YELLOW		+IN	Banana_COLOR
P2	Banana plug	WHITE		-IN	Banana_COLOR
P3	Banana plug	BLUE		OUT	Banana_COLOR
P5	Banana plug	RED		Vs	Banana_COLOR
P7	Banana plug	BLACK		GND	Banana_COLOR
U1	LMP8601	LMP8601			SOIC



# Appendix A Schematic





# Appendix B Layout





Figure 3. Layout, Silk Screen





#### **IMPORTANT NOTICE**

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All semiconductor products (also referred to herein as "components") are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its components to the specifications applicable at the time of sale, in accordance with the warranty in TI's terms and conditions of sale of semiconductor products. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by applicable law, testing of all parameters of each component is not necessarily performed.

TI assumes no liability for applications assistance or the design of Buyers' products. Buyers are responsible for their products and applications using TI components. To minimize the risks associated with Buyers' products and applications, Buyers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI components or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of significant portions of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI components or services with statements different from or beyond the parameters stated by TI for that component or service voids all express and any implied warranties for the associated TI component or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

Buyer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of TI components in its applications, notwithstanding any applications-related information or support that may be provided by TI. Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards which anticipate dangerous consequences of failures, monitor failures and their consequences, lessen the likelihood of failures that might cause harm and take appropriate remedial actions. Buyer will fully indemnify TI and its representatives against any damages arising out of the use of any TI components in safety-critical applications.

In some cases, TI components may be promoted specifically to facilitate safety-related applications. With such components, TI's goal is to help enable customers to design and create their own end-product solutions that meet applicable functional safety standards and requirements. Nonetheless, such components are subject to these terms.

No TI components are authorized for use in FDA Class III (or similar life-critical medical equipment) unless authorized officers of the parties have executed a special agreement specifically governing such use.

Only those TI components which TI has specifically designated as military grade or "enhanced plastic" are designed and intended for use in military/aerospace applications or environments. Buyer acknowledges and agrees that any military or aerospace use of TI components which have *not* been so designated is solely at the Buyer's risk, and that Buyer is solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI has specifically designated certain components as meeting ISO/TS16949 requirements, mainly for automotive use. In any case of use of non-designated products, TI will not be responsible for any failure to meet ISO/TS16949.

Products		Applications		
Audio	www.ti.com/audio	Automotive and Transportation	www.ti.com/automotive	
Amplifiers	amplifier.ti.com	Communications and Telecom	www.ti.com/communications	
Data Converters	dataconverter.ti.com	Computers and Peripherals	www.ti.com/computers	
DLP® Products	www.dlp.com	Consumer Electronics	www.ti.com/consumer-apps	
DSP	dsp.ti.com	Energy and Lighting	www.ti.com/energy	
Clocks and Timers	www.ti.com/clocks	Industrial	www.ti.com/industrial	
Interface	interface.ti.com	Medical	www.ti.com/medical	
Logic	logic.ti.com	Security	www.ti.com/security	
Power Mgmt	power.ti.com	Space, Avionics and Defense	www.ti.com/space-avionics-defense	
Microcontrollers	microcontroller.ti.com	Video and Imaging	www.ti.com/video	
RFID	www.ti-rfid.com			
OMAP Applications Processors	www.ti.com/omap	TI E2E Community	e2e.ti.com	
Wireless Connectivity	www.ti.com/wirelessconnectivity			

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2013, Texas Instruments Incorporated