

# Model C3235

## Washdown Checkweigher



- **Accuracy**–  $\pm 2$  divisions at full load
- **Capacity**–
  - 3 kg x 0.0005 kg (6 lb x 0.001 lb)
  - 6 kg x 0.001 kg (12 lb x 0.002 lb)
  - 15 kg x 0.002 kg (30 lb x 0.005 lb)
- **Construction**– Stainless steel and ABS plastic washdown enclosure
- **Display**– 6-digit, 13 mm (0.5") high 7-segment bright red LED display accept, over, under LED
- **Power**– Built-in rechargeable battery
- **Operator Keys**–Off, Zero, Function, Tare
- **Platform Size**– 229 mm (9") W x 190 mm (7.5" ) D

# Model C3235 Washdown Checkweigher

## Features

The C3235 is a washdown checkweigher for the rapid indication of weight and over, under, accept tolerances in washdown environment.

Totally portable the C3235 has an internal rechargeable battery which gives approximately 20 hours of usage between charges or can be operated direct from mains power supply.

Available in a choice of 3 kg (6 lb), 6 kg (12 lb) and 15 kg (30 lb) capacities with resolution of 1 part in 6000 the C3235 is an accurate scale built to work in harsh, wet environments such as portion control, food processing, meat preparation areas, catering kitchens, etc.

Washable and corrosion free the C3235 has a 229 mm x 190 mm (9" x 7.5") platform and a bright red LED display with 13 mm (0.5") high digits.

Simple to operate the keyboard has four buttons – off, on/zero, push button tare and function. The function key gives access to the checkweigher set up for targets and tolerances, unit switching and count modes.

C3235 has an auto off feature, which can be disabled, to switch the scale off after 10 minutes of inactivity. An audible buzzer is included which sounds when the weight is within the accept range – this can be switched off also.

A battery charge indicator is built in to the display giving an instant check on the condition of the battery, the scale also displays battery low when recharging is required.



## Specifications

### Capacity–

3 kg x 0.5 g (6 lb x 0.001 lb)  
6 kg x 1 g (12 lb x 0.002 lb)  
15 kg x 2 g (30 lb x 0.005 lb)

**Platform Size–** 229 mm (W) x 190 mm (D) x 13 mm (H)  
9" W x 7 ½" D x 0.5" H

**Construction–** Stainless steel and ABS plastic washdown enclosure

**Display–** Sealed watertight 7-segment, 6-digit, 13 mm (0.5") high red LED with annunciators

**Annunciators–** kg, g, lb, oz, tare, over, under, accept, count, zero, and battery voltage

**Keyboard–** On/Zero, Off, Tare, Function  
Function key gives access to checkweigh targets (with audible alarm), unit switching and count.

**Unit–** lb.oz, lb, kg, g

**Functions–** Count, unit switching, checkweigh limits with alarm, auto off after 10 minutes of inactivity

**Power–** Internally mounted main/AC adapter and internal rechargeable battery (6V – 4.5Ah). Auto-off after 10 minutes of inactivity.

**Battery Life–** Approximately 20 hours (charge time is 12 hours)

**Operating Temp–** -5° C to 35° C (23° F to 95° F)

### Scale Dimensions–

235 mm (L) x 285 mm (W) x 110 mm (H)  
9.25" x 11" x 4"

**Weight–** 3.7 kg (8 lb)

### Packaging Dimensions–

337 mm (L) x 280 mm (W) x 146 mm (H)  
13.25" L x 11" W x 5.75" H

**Shipping Weight–** 4.5 kg (10 lb)

**Certifications–** Full FCC compliance, UL/CUL power adapter, CE, WEEE directive



a division of Avery Weigh-Tronix, LLC

## Salter Brecknell Weighing Products

Salter Brecknell Weighing Products  
P.O. Box 9533  
Smethwick, West Midlands B66 9TE  
Tel: 0870 444 6132  
Fax: 0870 010 2241  
Email: sales@salterbrecknell.co.uk  
www.salterbrecknell.co.uk

