

Einhell

EXPERT

GE-PH 2555 A Petrol Hedge Trimmer

Features

- Throttle lock (1)
- Ignition switch (2)
- Starter handle (3)
- Low vibrating 2-stroke engine
- Vibration-absorbing additional handle (4)
- Hand guard (5)
- Laser cut, double cutting safety blades made of precision-ground special steel (6)
- Stop lever for rotating handle
- Throttle lever (7)
- Rotating handle +90°/0°/-90° (8)
- Quick start system for easy starting (**Auto choke**)
- Primer (manual fuel pump) for fast starting after a long break
- Centrifugal clutch for cutting attachment
- Anti vibration system
- Large petrol filler opening

Technical Data


- Power: **0.85 kW / 1.15 PS**
- Motor: 2-stroke
- Capacity: 24.5 cm³
- Fuel: gasoline (lead free); E10 qualified
- Cutting length: 55 cm
- Cutting thickness: max. 19 mm
- Petrol tank volume: 0.33 l
- Cuts per minute: 1,900
- Product weight: 5.5 kg

Logistic Data

- Net weight: 5.7 kg
- Gross weight: 7.1 kg
- Packing dimensions: 1120 x 240 x 220 mm
- Bar code: 4006825 585186
- Sales unit: 1 pc



TURNABLE HANDLE



**EASY STARTING SYSTEM
AUTO-CHOK**



ANTI-VIBRATION



LASERCUT KNIFE



**DIAMOND
GRINDED**

