



Einhell

GH-PC 1535 TC Petrol Chain Saw

Features

- Safety trigger
- Auto choke, primer and electronic ignition – for quick starting
- Chain brake / hand guard – stops the chain within a few milliseconds in case of kickback
- High-quality chain from OREGON
- OREGON-sprocket tip bar
- Chain catch – prevents from risks of chain jumping off cutter rail
- Anti-vibration design – cushions shocks and reduces user fatigue
- Automatic lubrication of cutter rail and chain
- Large claw stop
- Full crank shaft
- Centrifugal clutch for cutting attachment
- Toll-free chain tension

Standard accessories

- Fuel/ oil mixing bottle
- Cutter rail cover
- Spark plug key

Technical Data

- Displacement: 41 cc
- Capacity chain oil: 210 ml
- Capacity fuel: 260 ml
- Sword length: 14" (35 cm)
- Cutting speed: 21 m/s
- Power: **1.5 kW**
- Product weight: 5.5 kg

Logistic Data

- Net weight: 5.5 kg
- Gross weight: 5.7 kg
- Packing dimensions: 440 x 260 x 280 mm
- Bar code: 4006825 596397
- Sales unit: 1 pc

