




Einhell

HOME

TH-VC 1815 Vacuum Cleaner

The TH-VC 1815 is an all-round vacuum cleaner. You can clean rough, fine and dry or wet dirt even liquid without any problems. The throughput of the wet-dry vacuum cleaner is stopped automatically due to a protection float switch when liquid is suctioned and the vessel is filled.

Features

- 36 mm tube system (1)
- Carrying handle (2)
- 15 l plastic vessel (3)
- 4 pcs castors (4)
- Accessory bracket (5)
- Cable bracket (6)
- Blow adapter (7)

Technical Data

- | | |
|-----------------------|---------------|
| ■ Mains voltage: | 230 V ~ 50 Hz |
| ■ Input power: | 1,250 W |
| ■ Suction power max.: | 180 mbar |
| ■ Air quantity: | 65 l/ s |
| ■ Vessel capacity: | 15 l |
| ■ Product weight: | 4.2 kg |

Logistic Data

- | | |
|-----------------------|--------------------|
| ■ Net weight: | 4.2 kg |
| ■ Gross weight: | 5.0 kg |
| ■ Packing dimensions: | 330 x 330 x 440 mm |
| ■ Bar code: | 4006825 585179 |
| ■ Sales unit: | 1 pc |

Standard accessories

- 1 suction hose Ø 36 mm (1)
- 1 dust collection bin (8)
- 1 foam filter (9)
- 1 crevice nozzle (10)
- 1 adapter (11)
- 3 extension pipes Ø 36 mm (12)
- 1 large suction nozzle (13) with combi attachment for carpets and smooth floors




7



6



5



13

12

11



1

2

3

4