

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:19199-0008

Status:Active

Overview:Splices

Description:Avikrimp™ Window Butt Connector for 18-22 AWG Wire, Mylar Tape Carrier

Documents:

Drawing (PDF)

Product Specification PS-19902-015 (PDF)

Product Specification PS-19902-011 (PDF)

RoHS Certificate of Compliance (PDF)

General

Product Family

Series

Comments

Crimp Quality Equipment

Mil-Spec

Overview

Product Name

UPC

Splices

19199

Mil Spec M7928/5-3

Yes

M7928/5-3

Splices

Avikrimp™, Butt - Window

800753046818

Physical

Barrel Type

Color - Resin

Insulation

Material - Metal

Material - Plating Mating

Material - Plating Termination

Net Weight

Packaging Type

Temperature Range - Operating

Wire Insulation Diameter

Wire Size AWG

Wire Size mm²

Closed

Red

Nylon (PA)

Copper

Tin

Tin

1.194/g

Adhesive Tape on Reel

-55°C to +105°C

3.56mm max.

18, 20, 22

0.25 - 1.50

Electrical

Voltage - Maximum

300V

Material Info

Old Part Number

WA-840T

Reference - Drawing Numbers

Product Specification

Sales Drawing

PS-19902-011, PS-19902-015

SD-19199-003



image - Reference only

Series

EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Contains SVHC: No

Low-Halogen Status

Low-Halogen

China RoHS

Need more information on product environmental compliance?

Email productcompliance@molex.com

For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

19199Series

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Mini-Mac Applicator	0638859100
Air Feed-Mylar Tape	
Crimp Dies for	0192880043
MTA-100 Tape	
Applicator used in	
3BF Press, MTA-105	
Tape Applicator used	
in TM-2000™ Press,	
and ATP-301 Air	
Crimping Press for	
Mylar Tape Mounted	
Terminals	

This document was generated on 10/03/2014

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION