

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

26-48-1125

Status:

Active

Overview:

KK® Interconnect System - Molex

Description:

KK® 396 Breakaway Header, Vertical, Square Pin, with Friction Lock, 12 Circuits, Tin (Sn) Plating



Series

image - Reference only

Documents:

- [3D Model](#)
- [Drawing \(PDF\)](#)
- [Product Specification PS-08-50 \(PDF\)](#)
- [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA

LR19980

UL

E29179

General

Product Family

PCB Headers

Series

41671

Application

Power, Wire-to-Board

Application Tooling Part Link

11-20-0901

Overview

KK® Interconnect System - Molex

Product Name

KK® 396

UPC

800753586611

Physical

Breakaway

Yes

Circuits (Loaded)

12

Circuits (maximum)

12

Color - Resin

Black

Durability (mating cycles max)

25

Flammability

94V-0

Glow-Wire Compliant

No

Lock to Mating Part

Yes

Material - Metal

Brass

Material - Plating Mating

Tin

Material - Plating Termination

Tin

Material - Resin

Polyester

Net Weight

3.900/g

Number of Rows

1

Orientation

Vertical

PC Tail Length

4.37mm

PCB Locator

No

PCB Retention

None

PCB Thickness - Recommended

1.60mm

Packaging Type

Bag

Pitch - Mating Interface

3.96mm

Pitch - Termination Interface

3.96mm

Plating min - Mating

5.080µm

Plating min - Termination

5.080µm

Polarized to Mating Part

Yes

Polarized to PCB

No

Shrouded

Partial

Stackable

No

Temperature Range - Operating

See Product Specification

Termination Interface: Style

Through Hole

Electrical

EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Contains SVHC: No

Low-Halogen Status

Not Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

41671Series

Mates With

[2139](#) KK® Crimp Housing, [41695](#) KK® Crimp Housing, [6442](#) KK® Crimp Housing, [2145](#) PCB Connector, [41815](#) PCB Connector, [3069](#) KK® Crimp Housing

Current - Maximum per Contact	7A
Voltage - Maximum	250V
Solder Process Data	
Duration at Max. Process Temperature (seconds)	5
Lead-free Process Capability	Wave Capable (TH only)
Max. Cycles at Max. Process Temperature	1
Process Temperature max. C	235
Material Info	
Old Part Number	A-41671-A12A197
Reference - Drawing Numbers	
Product Specification	PS-08-50
Sales Drawing	SD-41671-001

This document was generated on 10/15/2014

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION