



Dimensions mm[inch]
 tolerances acc. to DIN ISO 2768-m
 Toleranzen gem. DIN ISO 2768-m

Isometric
 Scale 1:1
 Maßstab 1:1



| Mag. values DIN IEC 60404-8- | Conditions | Min | Typ | Max | Unit |
|------------------------------|---------------------------|------------------|-----|-----|-----------|
| Remanence Br | | 430 | 450 | | mT |
| Coercivity HcB | | 215 | 239 | | kA/m |
| Coercivity HcJ | | 217 | 241 | | kA/m |
| Max. operating temperature | | | | 100 | °C |
| Magnetic moment | inclusive of 5% tolerance | | | | E-6 Vs*cm |
| Magnet Material | | Hard Ferrit, Y35 | | | |
| Direction of Magnetization | | axial | | | |

| General data | Conditions | Min | Typ | Max | Unit |
|--------------|------------|--|-----|-----|------|
| Total weight | | 3,8 | 4,2 | 4,7 | g |
| Remark | | material of float: PP, grey RAL 7037 | | | |
| Remarks | | All details according to manufacturers information | | | |
| Remarks | | Magnet part number: 4001311093 | | | |