

Product information

18V COMBI DRILL LXT



DHP453RFE

Voltage	18 v
Max. in wood	36 mm
Max. in masonry	13 mm
Max. in steel	13 mm
Blows per minute	H: 0-19500/ L: 0-6000 bpm
Max Torque S/H	42 Nm
Torque Settings	16 + drill
No Load Speed	H: 0 - 1300 / L: 0 - 400 rpm
Battery Type	Lithium-ion
Battery Quantity (3.0 Ah)	2
Vibration: Drilling	2.5 m/sec ²
Vibration: Hammer Drilling	7.5 m/sec ²
Vibration K factor	1.5 m/sec ²



STANDARD EQUIPMENT: 194204-5 18V Li-ion battery, P-48701 DOUBLE ENDED BITS 45 - 150MM

- 22 minute charge time with the air cooled Makstar Optimum Charging System.
- Lithium-ion batteries have greater life spans than their Ni-MH or Ni-Cad counterparts giving 430% greater run time.
- Lithium-ion's 40% weight saving means 18 volt power can be obtained by a battery that weighs the same as a 12 volt Ni-MH battery.
- Conveniently located push button for forward and reverse.
- High comfort grips.
- Two speed gear box.
- Metal gears

Details correct as of: 25-11-2014

Makita reserve the right to change specifications at any time owing to their policy of constant improvement.

Accessories shown are not necessarily supplied.

www.makita.com