

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

16-02-1112

Status:

Active

Overview:

C-Grid® Products

Description:

SL™ Crimp Terminal, Series 71851, Female, with Tin (Sn) Plated Contact, 24-30 AWG, Reel

Documents:

Drawing (PDF)

Product Specification PS-70400 (PDF)


Product Specification PS-71851 (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	Crimp Terminals
Series	71851
Application	Signal
Crimp Quality Equipment	Yes
Overview	C-Grid® Products
Packaging Alternative	16-02-1116 (Loose)
Product Name	SL™
UPC	800753595781
Physical	
Gender	Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.060/g
Packaging Type	Reel
Plating min - Mating	3.810µm
Plating min - Termination	1.905µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.52mm max.
Wire Size AWG	24, 26, 28, 30
Wire Size mm²	N/A

Material Info	
Old Part Number	71851-0004

Reference - Drawing Numbers	
Product Specification	PS-70400, PS-71851
Sales Drawing	SD-71851-0004



EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Contains SVHC: No

Low-Halogen Status

Low-Halogen

China RoHS

Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

71851Series

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Hand Crimp Tool	0638258800
For SL™ Crimp Terminals	
Insertion Tool	0011020022
FineAdjust™	0639001500
Applicator	
T2 Terminator	0639103100
Tooling Die	
FineAdjust™	0639003100
Applicator for Female Crimp Terminal, 24-30 AWG Wire	
Extraction Tool	0011030036

This document was generated on 10/15/2014

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION