


# SEP8705

## AlGaAs Infrared Emitting Diode

### FEATURES

- T-1 package
- 15° (nominal) beam angle
- 880 nm wavelength
- Consistent optical properties
- Higher output power than GaAs at equivalent drive currents
- Mechanically and spectrally matched to SDP8405/8425 phototransistor and SDP8105 photodarlington




### DESCRIPTION

The SEP8705 is an aluminum gallium arsenide infrared emitting diode transfer molded in a T-1 smoke gray plastic package. Transfer molding of this device assures superior optical centerline performance compared to other molding processes. These devices typically exhibit 70% greater power intensity compared to GaAs devices at the same forward current. Lead lengths are staggered to provide a simple method of polarity identification.

### OUTLINE DIMENSIONS in inches (mm)

Tolerance	3 plc decimals	$\pm 0.005(0.12)$
	2 plc decimals	$\pm 0.020(0.51)$



# SEP8705

## AlGaAs Infrared Emitting Diode

### ELECTRICAL CHARACTERISTICS (25°C unless otherwise noted)

PARAMETER	SYMBOL	MIN	TYP	MAX	UNITS	TEST CONDITIONS
Irradiance <sup>(1)</sup>	H	0.54			mW/cm <sup>2</sup>	I <sub>F</sub> =20 mA
SEP8705-001		1.4		5.6		
SEP8705-002		2.7		7.8		
SEP8705-003						
Forward Voltage	V <sub>F</sub>			1.7	V	I <sub>F</sub> =20 mA
Reverse Breakdown Voltage	V <sub>BR</sub>	3.0			V	I <sub>R</sub> =10 μA
Peak Output Wavelength	λ <sub>p</sub>		880		nm	
Spectral Bandwidth	Δλ		80		nm	
Spectral Shift With Temperature	Δλ <sub>p</sub> /ΔT		0.2		nm/°C	
Beam Angle <sup>(2)</sup>	Ø		15		degr.	I <sub>F</sub> =Constant
Radiation Rise And Fall Time	t <sub>r</sub> , t <sub>f</sub>		0.7		μs	

Notes

1. Measured in mW/cm<sup>2</sup> into a 0.081(2.05) diameter aperture placed 0.40(10.16) from the lens tip.
2. Beam angle is defined as the total included angle between the half intensity points.

### ABSOLUTE MAXIMUM RATINGS

(25°C Free-Air Temperature unless otherwise noted)


Continuous Forward Current	50 mA
Power Dissipation	70 mW <sup>(1)</sup>
Operating Temperature Range	-40°C to 85°C
Storage Temperature Range	-40°C to 85°C
Soldering Temperature (5 sec)	240°C

Notes

1. Derate linearly from 25°C free-air temperature at the rate of 0.18 mW/°C.

### SCHEMATIC

INFR-A-1 SCH



Honeywell reserves the right to make changes in order to improve design and supply the best products possible.

# Honeywell

# SEP8705

## AlGaAs Infrared Emitting Diode

Fig. 1 Radiant Intensity vs Angular Displacement




Fig. 2 Radiant Intensity vs Forward Current




Fig. 3 Forward Voltage vs Forward Current




Fig. 4 Forward Voltage vs Temperature




Fig. 5 Spectral Bandwidth





Fig. 6 Coupling Characteristics with SDP8405




All Performance Curves Show Typical Values

# SEP8705

## AlGaAs Infrared Emitting Diode

Fig. 7 Relative Power Output vs Free Air Temperature



INFRAGRA

Honeywell reserves the right to make changes in order to improve design and supply the best products possible.

**Honeywell**