


NOTES:

1. MATERIALS
1. 1 CABLE: (7/0. 12BC*1P+7/0. 12BC+FAM)*2PCS+7/0. 20TC*2C+7/0. 12TC*1P+AM+7/0. 12TC+128/0. 12ALM+TRANSPARENT (0004) PVC JACKET
 OD=ø5.5 ± 0.15MM.
- CABLE PRINTING: USB 3.0 SUPER SPEED CABLE
1. 2 P1: USB 3.0 A TYPE MALE: SOLDER TYPE, BLUE PBT INSULATION, GOLD FLASH CONTACTS, NICKEL PLATED SHELL.
1. 3 P2: USB 3.0 B TYPE MALE: SOLDER TYPE, BLUE PBT INSULATION, GOLD FLASH CONTACTS, NICKEL PLATED SHELL.
1. 4 ALL HOOD: MOLDED TRANSPARENT (0004) PVC.
2. TESTING: 100% OPEN AND SHORT TEST.
3. PACKING: 1PC/PE BAG.
4. ALL MATERIAL BE ROHS COMPLIANT.

PIN OUT



SHELL (BRAID+DRAIN) SHELL



REV. 01		FROM CS14565 TO CS28249	2014-11-13	LENGTH TOLERANCE: X: ± 0.5		SCALE: FREE	CUS. NAME: CPC		PRODUCT NO:	CUSTOMER NO:	ENG:
REV. 00		NEW ISSUE	2014-11-12	X ± 0.2		UNIT: mm	PAGE: 1/1		DRAWING NO: 1059	CS28249	Mr. Zhang
REV. ECN.		MODIFY DESCRIPTION	DATE	X ± 0.1		VERSION: 01	PAGE: 1/1		PRODUCT DESCRIPTION: USB3.0 AM/BM		APPROVED:
1		2		3		4		5		6	
A		B		C		D		E		F	