



PIN OUT

AM ——— AM

- 1 ——— 1
2 ——— 2
3 ——— 3
4 ——— 4
5 ——— 5
6 ——— 6
7 ——— 7
8 ——— 8
9 ——— 9

SHELL (BRAID+DRAIN) ——— SHELL



- NOTES:
1. MATERIALS
1. 1 CABLE: (7/0.12BC*1P+7/0.12BC+FAM)*2PCS+7/0.20TC*2C+7/0.12TC*1P+AM+7/0.12TC+128/0.12ALM+TRANSPARENT (0004) PVC JACKET
- OD=ø5.5 ± 0.15MM.
- CABLE PRINTING:USB 3.0 SUPER SPEED CABLE
1. 2 P1: USB 3.0 A TYPE MALE: SOLDER TYPE, BLUE PBT INSULATION, GOLD FLASH CONTACTS,NICKEL PLATED SHELL.
1. 3 ALL HOOD: MOLDED TRANSPARENT (0004) PVC.
2. TESTING: 100% OPEN AND SHORT TEST.
3. PACKING: 1PC/PE BAG.
4. ALL MATERIAL BE ROHS COMPLIANT.

										LENGTH TOLERANCE:		SCALE:		CUS. NAME:		ENG:	
										X. ± 0.5		FREE		CPC		Mr. Zhang	
										X ± 0.2							
										.XX ± 0.1							
										ANGLE TOLERANCE:		UNIT:					
										X° ± 3°		mm					
										X° ± 1°		VERSION:		PAGE:		1/1	
												01					