


NOTES:
1. MATERIALS

- 1.1 CABLE: (7/0.12BC*1P+7/0.12BC+FAM)*2PCS+7/0.20TC*2C+7/0.12TC*1P+AM+7/0.12TC+128/0.12ALM+WHITE (4010)PVC JACKET
OD=∅5.5 ± 0.15MM.
CABLE PRINTING:USB 3.0 SUPER SPEED CABLE
- 1.2 P1: USB 3.0 A TYPE MALE: SOLDER TYPE, BLUE PBT INSULATION, GOLD FLASH CONTACTS, NICKEL PLATED SHELL.
- 1.3 ALL HOOD: MOLDED WHITE (4010) PVC.
2. TESTING: 100% OPEN AND SHORT TEST.
3. PACKING: 1PC/PE BAG.
4. ALL MATERIAL BE ROHS COMPLIANT.

PIN OUT



LENGTH TOLERANCE:		SCALE:		CUS. NAME:		ENG:	
X: ± 0.5		FREE		CPC		Mr. Zhang	
X ± 0.2		UNIT: mm		PAGE: 1/1		CHECKED:	
X ± 0.1		VERSION: 01		DRAWING NO: 1064		APPROVED:	
ANGLE TOLERANCE:		PRODUCT NO:		PRODUCT DESCRIPTION:		CUSTOMER NO: CS28254	
X° ± 1°		DRAWING NO: 1064		USB3.0 AM/AM			

REV.	ECN.	MODIFY DESCRIPTION	DATE	1	2	3	4	5	6	7
01		FROM CS14578 TO CS28254	2014-11-13							
00		NEW ISSUE	2014-11-12							