


Rigid and Intermediate Metal Conduit Fittings

Available in your choice of steel/malleable iron, aluminum or stainless steel.

Locknuts



- Steel from 1/4" to 2", malleable iron from 2 1/2" to 6"
- Aluminum 624 or Type 304 stainless steel all sizes



STL./M.I.	CAT. NO.		SIZE (IN.)	DIMENSIONS (IN.)	
	ALUM.	ST. STL.		A	B
139*	—	—	1/4	3/4	9/64
140*	—	—	3/8	1 1/16	9/64
141**	141AL	141-SST	1/2	1 1/4	5/32
142**	142AL	142-SST	3/4	1 3/8	3/16
143	143AL	143-SST	1	1 11/16	13/64
144	144AL	144-SST	1 1/4	2 1/2	13/64
145	145AL	145-SST	1 1/2	2 1/2	13/64
146	146AL	146-SST	2	3	7/32
147	147AL	—	2 1/2	3 3/16	13/32
148	148AL	—	3	4 3/16	13/32
149	149AL	—	3 1/2	4 13/16	7/32
150	150AL	—	4	5 5/16	15/32
151	151AL	—	4 1/2	5 15/16	17/32
152	152AL	—	5	6 1/2	17/32
153	153AL	—	6	7 3/4	19/32

* Hex shape

** Case hardened locknuts

Aluminum locknuts comply with federal standard of copper-free aluminum; less than .5% copper.


Available with DURA-PLATE® Finish.

UL File E-23018

CSA File No. 2884

Ensures positive bonding of conduit to box and prevents loosening due to vibration!

Bonding Locknuts



- Steel or malleable iron (steel through 2")
- Can be used anywhere an ordinary locknut is installed
- Also can be used for Service Entrance applications in conformance with code
- T&B rigid conduit and EMT (thinwall) fittings comply with Federal Specification A-A-50553



CAT. NO.	SIZE (IN.)	DIMENSIONS (IN.)	
		A	B
106†	1/2	1 1/8	.125
107†	3/4	1 1/8	.140
108	1	1 15/16	.170
109	1 1/4	2 1/2	.170
110	1 1/2	2 1/2	.170
111	2	3	.187
112†	2 1/2	3 3/32	.375
113†	3	4 1/16	.375
114†	3 1/2	4 29/32	.438
115†	4	5 1/2	.438

† Not CSA certified.


Available with DURA-PLATE® Finish.

UL File No. E-3060

CSA File No. 638

Provides positive seal against water and oil.

Sealing Locknuts



- For use with rigid and intermediate metal conduits or fittings
- Provides watertight or raintight seal at all enclosures



CAT. NO.	SIZE (IN.)	DIMENSIONS (IN.)		
		A	B	C
141SL	1/2	1.140	1/8	1/4
142SL	3/4	1.420	3/16	3/16
143SL	1	1.770	1/4	3/16
144SL	1 1/4	2.281	1/4	3/16
145SL	1 1/2	2.598	1/4	3/16
146SL	2	3.175	3/16	3/16

UL File No. E-23018

CSA File No. 2884

United States
Tel: 901.252.8000
800.816.7809
Fax: 901.252.1354

Technical Services
Tel: 888.862.3289

Thomas & Betts

www.tnb.com