



Main

Range of product	Harmony XAR
Product or component type	Hand-held remote control
Device short name	ZART
Control button type	2 configurable auxiliary push-button 6 configurable motion push-button

Complementary


Material	Protective cover : EPDM rubber Cover : PP (polypropylene) Enclosure : PBT (polybutylene terephthalate) Enclosure : PC (polycarbonate)
Function available	Vibrator function Accelerometer function
Display type	LCD display 34 x 42 mm
Operating distance	50 m
Mechanical robustness	4.5 m free fall resistance conforming to IEC 60068-2-27
Communication network type	Wireless : Bluetooth low energy
Transmission frequency	2.4 GHz
Maximum sensing distance	100 m in free field
Response time	< 300 ms at full duplex
Charging time	900 s
Autonomy	16 h
Battery type	Rechargeable
Mechanical durability	5000000 cycles
Service life	5 yr
Width	100 mm
Height	340 mm
Depth	90 mm
Product weight	0.65 kg

Environment

Radio agreement	ANATEL SRRRC FCC RSS ICASA ARIB
IP degree of protection	IP65
NEMA degree of protection	NEMA 4
Ambient air temperature for operation	> -20...60 °C
Ambient air temperature for storage	> -20...45 °C
Operating altitude	0...2000 m

Storage altitude	0...3000 m
Vibration resistance	0.075 mm (f= 10...55 Hz) conforming to IEC 60068-2-6
Shock resistance	100 gn conforming to IEC 60068-2-27
Relative humidity	0...95 % (temperature : > -20...60 °C) (operating)
Product certifications	CE CSA C-Tick UL EAC JIS KC

Offer Sustainability

Sustainable offer status	Green Premium product
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available  Download Product Environmental
Product end of life instructions	Available

Dimensions

