


ECN NO.	REV	DESCRIPTION	DATE	REVISER	APPROVED
---------	-----	-------------	------	---------	----------



P1	P2
1 _____	1 _____
2 _____	2 _____
3 _____	3 _____
4 _____	4 _____
5 _____	5 _____
6 _____	6 _____
7 _____	7 _____
8 _____	8 _____
9 _____	9 _____
10 _____	10 _____
	11 _____
	12 _____
	13 _____
	14 _____
	15 _____
	16 _____
	17 _____
	18 _____
	20 _____
	21 _____
	22 _____
	23 _____
	24 _____
	25 _____
	SHELL _____

ELECTRICAL CHARACTER:

- 100% OPEN & SHORT TESTING.
- WITHSTANDING VOLTAGE: DC 300V 0.01SEC.
- INSULATION RESISTANCE: 5M OHMS MIN.
- CONDUCTIVE RESISTANCE: 3 OHMS MAX.

GENERAL TOLERANCES (UNLESS SPECIFIED)		CUST PART NO.:	
.XXX: ±0.15	ANGULAR: ±3°	DESIGN: KEVIN	SCALE: NONE
.XX: ±0.25		CHECKED: KEVIN	UNIT: mm
.X: ±0.50		APPROVED:	TITLE: DB 25P M TO DB 25P F CABLE
ITEM	DESCRIPTION	UNIT	QT'Y
1	CABLE: 30AWG(7/0.10)x25C+DRAIN+AL/MYLAR,OD:6.6 PVC JACKET,BEIGE WHITE.	mm	625
2	CONN: DB 25P F,CONTACT:TIN PLATED,SHELL:NICKEL PLATED,BLUE INSULATOR.	PCS	1
3	CONN: DB 25P M,CONTACT:GOLD PLATED,SHELL:NICKEL PLATED,BLUE INSULATOR.	PCS	1
4	SCREW: #4-40UNC STEEL,NICKEL PLATED.	PCS	4
5	PE: LD-PE,NATURAL.	g	25
6	PVC: BEIGE WHITE.	g	30



DATE: 2010.11.18
SHEET NO.: 1 OF 1