

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

19073-0167

Status:

Active

Overview:

Solderless Terminals

Description:

Avikrimp™ Ring Tongue Terminal for 10 to 12 AWG Wire, Stud Size 8 (M4), Length 27.71mm, Mylar Tape Carrier

Documents:

Drawing (PDF)

Product Specification PS-19902-011 (PDF)

Product Specification PS-19902-015 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

CSA

LR18689

UL

E32244

General

Product Family

Ring and Spade Terminals

Series

19073

Crimp Quality Equipment

Yes

Mil-Spec

N/A

Overview

Solderless Terminals

Product Name

Avikrimp™

Type

Ring

UPC

800753076952

Physical

Barrel Type

Closed

Flammability

94V-2

Insulation

Nylon (PA)

Material - Plating Mating

Tin

Net Weight

2.270/g

Packaging Type

Adhesive Tape on Reel

Stud Size

8 (M4)

Wire Insulation Diameter

5.70mm max.

Wire Size AWG

10, 12

Wire Size mm²

0.40 - 0.60

Material Info

Old Part Number

C-828-08T


Reference - Drawing Numbers

Product Specification

PS-19902-011, PS-19902-015

Sales Drawing

SD-19073-007



Series

image - Reference only

EU RoHS

ELV and RoHS Compliant

REACH SVHC

Contains SVHC: No

Low-Halogen Status

Low-Halogen

China RoHS

Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

19073Series

Application Tooling | FAQ
Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
Mini-Mac™	0638851500
Applicator	
Crimp Dies for	0192880179
MTA-100 Tape	
Applicator used in	
3BF Press, MTA-105	
Tape Applicator used	
in TM-2000™ Press,	
and ATP-301 Air	
Crimping Press for	
Mylar Tape Mounted	
Terminals	

This document was generated on 11/26/2014

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION