


LP2K0910BD

TeSys K reversing contactor - 3P(3 NO) - AC-3
- <= 440 V 9 A - 24 V DC coil



Main

Commercial Status	Commercialised
Range of product	TeSys K
Product or component type	Reversing contactor
Device short name	LP2K
Contactor application	Motor control Resistive load
Utilisation category	AC-1 AC-3 AC-4
Device presentation	Preassembled with reversing power busbar
Poles description	3P
Power pole contact composition	3 NO
[Ue] rated operational voltage	<= 690 V AC 50/60 Hz for signalling circuit 690 V AC 50/60 Hz for power circuit
[Ie] rated operational current	16 A (<= 70 °C) at 690 V AC AC-1 for power circuit 20 A (<= 50 °C) at <= 440 V AC AC-1 for power circuit 9 A at <= 440 V AC AC-3 for power circuit
Motor power kW	4 kW at 660...690 V AC 50/60 Hz 4 kW at 500...600 V AC 50/60 Hz 4 kW at 480 V AC 50/60 Hz 4 kW at 440 V AC 50/60 Hz 4 kW at 380...415 V AC 50/60 Hz 2.2 kW at 220...230 V AC 50/60 Hz
Control circuit type	DC standard
Control circuit voltage	24 V DC
Auxiliary contact composition	1 NO
[Uimp] rated impulse withstand voltage	8 kV
Overvoltage category	III
[Ith] conventional free air thermal current	10 A at <= 50 °C for signalling circuit 20 A at <= 50 °C for power circuit
Irms rated making capacity	110 A AC for signalling circuit conforming to IEC 60947 110 A AC for power circuit conforming to IEC 60947 110 A AC for power circuit conforming to NF C 63-110
Rated breaking capacity	70 A at 660...690 V conforming to IEC 60947 110 A at 380...400 V conforming to IEC 60947 110 A at 220...230 V conforming to IEC 60947 80 A at 500 V conforming to IEC 60947 110 A at 440 V conforming to IEC 60947 110 A at 415 V conforming to IEC 60947
[Icw] rated short-time withstand current	20 A <= 50 °C >= 15 s power circuit 110 A 100 ms signalling circuit 90 A 500 ms signalling circuit 80 A 1 s signalling circuit 40 A <= 50 °C 3 min power circuit 45 A <= 50 °C 1 min power circuit 60 A <= 50 °C 30 s power circuit 80 A <= 50 °C 10 s power circuit 85 A <= 50 °C 5 s power circuit 90 A <= 50 °C 1 s power circuit

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Associated fuse rating	10 A gG for signalling circuit conforming to VDE 0660 10 A gG for signalling circuit conforming to IEC 60947 25 A aM for power circuit 25 A gG at <= 440 V for power circuit
Average impedance	3 mOhm at 50 Hz - lth 20 A for power circuit
[Ui] rated insulation voltage	600 V for signalling circuit conforming to CSA C22.2 No 14 600 V for power circuit conforming to CSA C22.2 No 14 600 V for signalling circuit conforming to UL 508 690 V for signalling circuit conforming to IEC 60947-5-1 690 V for signalling circuit conforming to IEC 60947-4-1 690 V for power circuit conforming to IEC 60947-4-1 600 V for power circuit conforming to UL 508
Electrical durability	1.3 Mcycles 9 A AC-3 at Ue <= 440 V 0.18 Mcycles 20 A AC-1 at Ue <= 440 V
Interlocking type	Mechanical
Mounting support	Plate Rail
Standards	BS 5424 IEC 60947 NF C 63-110 VDE 0660
Product certifications	CSA UL
Connections - terminals	Screw clamp terminals 2 cable(s) 0.34...1.5 mm ² - cable stiffness: flexible - with cable end Screw clamp terminals 2 cable(s) 0.75...4 mm ² - cable stiffness: flexible - without cable end Screw clamp terminals 2 cable(s) 1.5...4 mm ² - cable stiffness: solid Screw clamp terminals 1 cable(s) 0.34...2.5 mm ² - cable stiffness: flexible - with cable end Screw clamp terminals 1 cable(s) 0.75...4 mm ² - cable stiffness: flexible - without cable end Screw clamp terminals 1 cable(s) 1.5...4 mm ² - cable stiffness: solid
Tightening torque	1.3 N.m - on screw clamp terminals - with screwdriver flat Ø 6 mm 1.3 N.m - on screw clamp terminals - with screwdriver Philips No 2
Operating time	10 ms coil de-energisation and NO opening 30...40 ms coil energisation and NO closing
Safety reliability level	B10d = 20000000 cycles contactor with mechanical load conforming to EN/ISO 13849-1 B10d = 1369863 cycles contactor with nominal load conforming to EN/ISO 13849-1
Mechanical durability	5 Mcycles
Operating rate	3600 cyc/h

Complementary

Control circuit voltage limits	0.1...0.75 Uc at <= 50 °C drop-out 0.8...1.15 Uc at <= 50 °C operational
Inrush power in W	3 W at 20 °C
Hold-in power consumption in W	3 W at 20 °C
Heat dissipation	3 W
Auxiliary contacts type	Type instantaneous 1 NO
Minimum switching current	5 mA for signalling circuit
Minimum switching voltage	17 V for signalling circuit
Non overlap distance	0.5 mm
Insulation resistance	> 10 MOhm for signalling circuit

Environment

IP degree of protection	IP2x conforming to VDE 0106
Protective treatment	TC conforming to DIN 50016 TC conforming to IEC 60068
Ambient air temperature for operation	-25...50 °C
Ambient air temperature for storage	-50...80 °C
Operating altitude	2000 m without derating in temperature
Flame retardance	Requirement 2 conforming to NF F 16-102 Requirement 2 conforming to NF F 16-101 V1 conforming to UL 94
Mechanical robustness	Shocks contactor closed, on Y axis 10 Gn for 11 ms IEC 60068-2-27 Shocks contactor closed, on X axis 15 Gn for 11 ms IEC 60068-2-27 Shocks contactor opened, on Y axis 6 Gn for 11 ms IEC 60068-2-27 Shocks contactor opened, on X axis 10 Gn for 11 ms IEC 60068-2-27 Vibrations contactor opened 2 Gn, 5...300 Hz IEC 60068-2-6 Vibrations contactor closed 4 Gn, 5...300 Hz IEC 60068-2-6 Shocks contactor opened, on Z axis 10 Gn for 11 ms IEC 60068-2-27 Shocks contactor closed, on Z axis 15 Gn for 11 ms IEC 60068-2-27
Height	58 mm
Width	90 mm
Depth	57 mm
Product weight	0.48 kg

RoHS compliance

RoHS EUR status	Compliant
RoHS EUR conformity date(YYYW)	0706

Contractual warranty

Period	18 months
--------	-----------