



Safety Data Sheet according to Regulation (EC) No 1907/2006

Page 1 of 8

LOCTITE SI 5368 BK known as 5368 BLACK 310ML GB

sds no. : 164824
V003.1

Revision: 16.10.2013
printing date: 18.12.2014

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

LOCTITE SI 5368 BK known as 5368 BLACK 310ML GB

1.2. Relevant identified uses of the substance or mixture and uses advised against

Intended use:
Silicone sealant

1.3. Details of the supplier of the safety data sheet

Henkel Limited
2 Bishop Square Business Park
AL109EY Herfordshire Hatfield

Great Britain

Phone: +44 1606 593933
Fax-no.: +44 1606 863762

ua-productsafety.uk@uk.henkel.com

1.4. Emergency telephone number

24 Hours Emergency Tel: +44 (0)1442 278497

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification (CLP):

Skin irritation	Category 2
H315 Causes skin irritation.	
Serious eye irritation	Category 2
H319 Causes serious eye irritation.	

Classification (DPD):

The product is not subject to classification according to the calculation methods of the "General Classification Guideline for Preparations of the EC" as issued in the last version.

2.2. Label elements

Label elements (CLP):

Hazard pictogram:



Signal word:

Warning

Hazard statement: H315 Causes skin irritation.
H319 Causes serious eye irritation.

Precautionary statement: P302+P352 IF ON SKIN: Wash with plenty of soap and water.
P337+P313 If eye irritation persists: Get medical advice/attention.

Label elements (DPD):

The product is not subject to classification according to the calculation methods of the "General Classification Guideline for Preparations of the EC" as issued in the last version.

Additional labeling:

Safety data sheet available for professional user on request.

2.3. Other hazards

None if used properly.

SECTION 3: Composition/information on ingredients

General chemical description:

Acetoxy curing silicone

Declaration of the ingredients according to CLP (EC) No 1272/2008:

Hazardous components CAS-No.	EC Number REACH-Reg No.	content	Classification
Methyltriacetoxysilane 4253-34-3	224-221-9	1 - < 3 %	Acute toxicity 4; Oral H302 Skin corrosion 1B H314

For full text of the H - statements and other abbreviations see section 16 "Other information".

Substances without classification may have community workplace exposure limits available.

Declaration of ingredients according to DPD (EC) No 1999/45:

Hazardous components CAS-No.	EC Number REACH-Reg No.	content	Classification
Methyltriacetoxysilane 4253-34-3	224-221-9	1 - < 3 %	R14 C - Corrosive; R34 Xn - Harmful; R22

For full text of the R-Phrases indicated by codes see section 16 'Other Information'.

Substances without classification may have community workplace exposure limits available.

SECTION 4: First aid measures

4.1. Description of first aid measures

Inhalation:

Move to fresh air. If symptoms persist, seek medical advice.

Skin contact:

IF ON SKIN: Wash with plenty of soap and water.
Seek medical advice.

Eye contact:

Rinse immediately with plenty of running water (for 10 minutes). Seek medical attention if necessary.

Ingestion:

Do not induce vomiting.
Seek medical advice.

4.2. Most important symptoms and effects, both acute and delayed

Causes serious eye irritation.

SKIN: Redness, inflammation.

4.3. Indication of any immediate medical attention and special treatment needed

See section: Description of first aid measures

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable extinguishing media:

Carbon dioxide, foam, powder

Fine water spray

5.2. Special hazards arising from the substance or mixture

Do not expose to direct heat.

carbon oxides.

Silica fume

Formaldehyde

5.3. Advice for firefighters

Wear self-contained breathing apparatus.

Additional information:

In case of fire, keep containers cool with water spray.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Avoid contact with skin and eyes.

Ensure adequate ventilation.

See advice in chapter 8

6.2. Environmental precautions

Do not let product enter drains.

6.3. Methods and material for containment and cleaning up

Scrape up as much material as possible.

Ensure adequate ventilation.

Store in a partly filled, closed container until disposal.

Dispose of contaminated material as waste according to Chapter 13.

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Use only in well-ventilated areas.

Vapours should be extracted to avoid inhalation.

Hygiene measures:

Wash hands before work breaks and after finishing work.

Do not eat, drink or smoke while working.

Good industrial hygiene practices should be observed.

7.2. Conditions for safe storage, including any incompatibilities

Store in a cool, well-ventilated place.

Never allow product to get in contact with water during storage

7.3. Specific end use(s)

Silicone sealant

SECTION 8: Exposure controls/personal protection**8.1. Control parameters****Occupational Exposure Limits**

Valid for
Great Britain

Ingredient	ppm	mg/m ³	Type	Category	Remarks
ACETIC ACID 64-19-7	10	25	Time Weighted Average (TWA):	Indicative	ECTLV

Biological Exposure Indices:

None

8.2. Exposure controls:

Respiratory protection:

Use only in well-ventilated areas.

Hand protection:

Chemical-resistant protective gloves (EN 374).

Suitable materials for short-term contact or splashes (recommended: at least protection index 2, corresponding to > 30 minutes permeation time as per EN 374):

nitrile rubber (NBR; \geq 0.4 mm thickness)

Suitable materials for longer, direct contact (recommended: protection index 6, corresponding to > 480 minutes permeation time as per EN 374):

nitrile rubber (NBR; \geq 0.4 mm thickness)

This information is based on literature references and on information provided by glove manufacturers, or is derived by analogy with similar substances. Please note that in practice the working life of chemical-resistant protective gloves may be considerably shorter than the permeation time determined in accordance with EN 374 as a result of the many influencing factors (e.g. temperature). If signs of wear and tear are noticed then the gloves should be replaced.

Eye protection:

Wear protective glasses.

Skin protection:

Wear suitable protective clothing.

SECTION 9: Physical and chemical properties**9.1. Information on basic physical and chemical properties**

Appearance	paste black
Odor	Acetic acid
Odour threshold	No data available / Not applicable
pH	not applicable
Initial boiling point	Not determined
Flash point	> 150 °C (> 302 °F)
Decomposition temperature	No data available / Not applicable
Vapour pressure	< 0,1 mm hg
Density ()	1,04 g/cm ³
Bulk density	No data available / Not applicable
Viscosity	No data available / Not applicable
Viscosity (kinematic)	No data available / Not applicable
Explosive properties	No data available / Not applicable
Solubility (qualitative) (Solvent: Water)	Partially soluble
Solubility (qualitative)	Insoluble

(Solvent: Acetone)	
Solubility (qualitative)	Polymerises in presence of water.
Solidification temperature	No data available / Not applicable
Melting point	No data available / Not applicable
Flammability	No data available / Not applicable
Auto-ignition temperature	No data available / Not applicable
Explosive limits	No data available / Not applicable
Partition coefficient: n-octanol/water	No data available / Not applicable
Evaporation rate	No data available / Not applicable
Vapor density	No data available / Not applicable
Oxidising properties	No data available / Not applicable

9.2. Other information

No data available / Not applicable

SECTION 10: Stability and reactivity

10.1. Reactivity

Strong oxidizing agents.
Polymerises in presence of water.

10.2. Chemical stability

Stable under recommended storage conditions.

10.3. Possibility of hazardous reactions

See section reactivity

10.4. Conditions to avoid

Stable under normal conditions of storage and use.

10.5. Incompatible materials

See section reactivity

10.6. Hazardous decomposition products

Acetic acid is liberated slowly upon contact with moisture.
At higher temperatures (>150C) may release formaldehyde (traces).

SECTION 11: Toxicological information

11.1. Information on toxicological effects

General toxicological information:

The mixture is classified based on the available hazard information for the ingredients as defined in the classification criteria for mixtures for each hazard class or differentiation in Annex I to Regulation 1272/2008/EC. Relevant available health/ecological information for the substances listed under Section 3 is provided in the following.

Oral toxicity:

This material is considered to have low toxicity if swallowed.

Inhalative toxicity:

Acetic acid is liberated slowly upon contact with moisture.
Inhalation of vapors in high concentration may cause irritation of respiratory system

Skin irritation:

Causes skin irritation.

Eye irritation:

Causes serious eye irritation.
Acetic acid released during polymerisation of acetoxy curing RTV silicones is irritating to the eyes

Acute oral toxicity:

Hazardous components CAS-No.	Value type	Value	Route of application	Exposure time	Species	Method
Methyltriacetoxysilane 4253-34-3	LD50	1.600 mg/kg	oral		rat	OECD Guideline 401 (Acute Oral Toxicity)

SECTION 12: Ecological information**General ecological information:**

The mixture is classified based on the available hazard information for the ingredients as defined in the classification criteria for mixtures for each hazard class or differentiation in Annex I to Regulation 1272/2008/EC. Relevant available health/ecological information for the substances listed under Section 3 is provided in the following.

Cured Loctite products are typical polymers and do not pose any immediate environmental hazards.

In the cured state contribution of this product to Environmental Hazards is insignificant in comparison to articles in which it is used.

Precautions required with respect to Environmental Hazards of articles in which this product is used should be considered.

12.1. Toxicity**Ecotoxicity:**

Do not empty into drains / surface water / ground water.

12.2. Persistence and degradability**Persistence and Biodegradability:**

The product is not biodegradable.

12.3. Bioaccumulative potential / 12.4. Mobility in soil**Mobility:**

Cured adhesives are immobile.

Bioaccumulative potential:

No data available.

12.5. Results of PBT and vPvB assessment

No data available.

12.6. Other adverse effects

No data available.

SECTION 13: Disposal considerations**13.1. Waste treatment methods****Product disposal:**

Dispose of in accordance with local and national regulations.

Disposal of uncleaned packages:

After use, tubes, cartons and bottles containing residual product should be disposed of as chemically contaminated waste in an authorised legal land fill site or incinerated.

Disposal must be made according to official regulations.

Waste code

08 04 09 waste adhesives and sealants containing organic solvents and other dangerous substances

SECTION 14: Transport information**14.1. UN number**

ADR	Not dangerous goods
RID	Not dangerous goods
ADNR	Not dangerous goods
IMDG	Not dangerous goods
IATA	Not dangerous goods

14.2. UN proper shipping name

ADR	Not dangerous goods
RID	Not dangerous goods
ADNR	Not dangerous goods
IMDG	Not dangerous goods
IATA	Not dangerous goods

14.3. Transport hazard class(es)

ADR	Not dangerous goods
RID	Not dangerous goods
ADNR	Not dangerous goods
IMDG	Not dangerous goods
IATA	Not dangerous goods

14.4. Packaging group

ADR	Not dangerous goods
RID	Not dangerous goods
ADNR	Not dangerous goods
IMDG	Not dangerous goods
IATA	Not dangerous goods

14.5. Environmental hazards

ADR	not applicable
RID	not applicable
ADNR	not applicable
IMDG	not applicable
IATA	not applicable

14.6. Special precautions for user

ADR	not applicable
RID	not applicable
ADNR	not applicable
IMDG	not applicable
IATA	not applicable

14.7. Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code

not applicable

SECTION 15: Regulatory information**15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture**VOC content < 5,00 %
(1999/13/EC)**15.2. Chemical safety assessment**

A chemical safety assessment has not been carried out.

SECTION 16: Other information

The labelling of the product is indicated in Section 2. The full text of all abbreviations indicated by codes in this safety data sheet are as follows:

- R14 Reacts violently with water.
- R22 Harmful if swallowed.
- R34 Causes burns.
- H302 Harmful if swallowed.
- H314 Causes severe skin burns and eye damage.

Further information:

This information is based on our current level of knowledge and relates to the product in the state in which it is delivered. It is intended to describe our products from the point of view of safety requirements and is not intended to guarantee any particular properties.