



## Safety Data Sheet according to Regulation (EC) No1907/2006

Page 1 of 10

SDS No. : 168430  
V003.1

Loctite 222

Revision: 27.01.2014  
printing date: 17.12.2014

### SECTION 1: Identification of the substance/mixture and of the company/undertaking

#### 1.1. Product identifier

Loctite 222

#### Contains:

Cumene hydroperoxide

#### 1.2. Relevant identified uses of the substance or mixture and uses advised against

Intended use:

Threadlocker

#### 1.3. Details of the supplier of the safety data sheet

Henkel Limited

2 Bishop Square Business Park

AL109EY Herfordshire Hatfield

Great Britain

Phone: +44 1606 593933

Fax-no.: +44 1606 863762

ua-productsafety.uk@uk.henkel.com

#### 1.4. Emergency telephone number

24 Hours Emergency Tel: +44 (0)1442 278497

### SECTION 2: Hazards identification

#### 2.1. Classification of the substance or mixture

##### Classification (CLP):

Serious eye irritation

Category 2

H319 Causes serious eye irritation.

Specific target organ toxicity - single exposure

Category 3

H335 May cause respiratory irritation.

Target organ: respiratory tract irritation

##### Classification (DPD):

Xi - Irritant

R36/37 Irritating to eyes and respiratory system.

#### 2.2. Label elements

##### Label elements (CLP):

**Hazard pictogram:**



**Signal word:**

Warning

**Hazard statement:**

H319 Causes serious eye irritation.  
H335 May cause respiratory irritation.

**Precautionary statement:**

\*\*\*For consumer use only: P101 If medical advice is needed, have product container or label at hand. P102 Keep out of reach of children. P501 Dispose of waste and residues in accordance with local authority requirements\*\*\*

**Precautionary statement:  
Prevention**

P261 Avoid breathing vapours.

**Precautionary statement:  
Response**

P337+P313 If eye irritation persists: Get medical advice/attention.

**Label elements (DPD):**

Xi - Irritant



**Risk phrases:**

R36/37 Irritating to eyes and respiratory system.

**Safety phrases:**

S23 Do not breathe vapour.  
S25 Avoid contact with eyes.  
S26 In case of contact with eyes, rinse immediately with plenty of water and seek medical advice.  
S51 Use only in well-ventilated areas.

**Additional labeling:**

For consumer use only: S2 Keep out of the reach of children.  
S46 If swallowed, seek medical advice immediately and show this container or label.

**2.3. Other hazards**

None if used properly.

**SECTION 3: Composition/information on ingredients**

**General chemical description:**

Product based on polyethylene glycol dimethacrylate.

**Declaration of the ingredients according to CLP (EC) No 1272/2008:**

Hazardous components CAS-No.	EC Number REACH-Reg No.	content	Classification
Cumene hydroperoxide 80-15-9	201-254-7	> 1 - < 3 %	Organic peroxides E H242 Acute toxicity 3; Inhalation H331 Acute toxicity 4; Dermal H312 Acute toxicity 4; Oral H302 Specific target organ toxicity - repeated exposure 2 H373 Chronic hazards to the aquatic environment 2 H411 Skin corrosion 1B H314
1,4-Naphthalenedione 130-15-4	204-977-6	> 0,01 - < 0,1 %	Acute toxicity 3; Oral H301 Skin irritation 2; Dermal H315 Skin sensitizer 1; Dermal H317 Serious eye irritation 2 H319 Acute toxicity 1; Inhalation H330 Specific target organ toxicity - single exposure 3; Inhalation H335 Acute hazards to the aquatic environment 1 H400 Chronic hazards to the aquatic environment 1 H410 M factor: 10

For full text of the H - statements and other abbreviations see section 16 "Other information".  
Substances without classification may have community workplace exposure limits available.

**Declaration of ingredients according to DPD (EC) No 1999/45:**

Hazardous components CAS-No.	EC Number REACH-Reg No.	content	Classification
Cumene hydroperoxide 80-15-9	201-254-7	> 1 - < 3 %	T - Toxic; R23 Xn - Harmful; R21/22, R48/20/22 C - Corrosive; R34 O - Oxidizing; R7 N - Dangerous for the environment; R51/53
Cumene 98-82-8	202-704-5	> 0,1 - < 0,9 %	R10 Xn - Harmful; R65 Xi - Irritant; R37 N - Dangerous for the environment; R51/53
1,4-Naphthalenedione 130-15-4	204-977-6	> 0,01 - < 0,1 %	T+ - Very toxic; R25, R26 Xi - Irritant; R36/37/38, R43 N - Dangerous for the environment; R50/53

For full text of the R-Phrases indicated by codes see section 16 'Other Information'.  
Substances without classification may have community workplace exposure limits available.

**SECTION 4: First aid measures****4.1. Description of first aid measures****Inhalation:**

Should not be a problem as product is of low volatility. However, if feeling unwell remove patient to fresh air.

**Skin contact:**

Wash skin with water  
In case of adverse health effects seek medical advice.

**Eye contact:**

Flush eyes with plenty of water for at least 5 minutes. If irritation persists seek medical attention.

**Ingestion:**

Rinse out mouth, drink 1-2 glasses of water, do not induce vomiting.  
In case of adverse health effects seek medical advice.

**4.2. Most important symptoms and effects, both acute and delayed**

**EYE:** Irritation, conjunctivitis.

**RESPIRATORY:** Irritation, coughing, shortness of breath, chest tightness.

Prolonged or repeated contact may cause skin irritation.

**4.3. Indication of any immediate medical attention and special treatment needed**

See section: Description of first aid measures

## SECTION 5: Firefighting measures

**5.1. Extinguishing media**

**Suitable extinguishing media:**

Foam, extinguishing powder, carbon dioxide.

**Extinguishing media which must not be used for safety reasons:**

None known

**5.2. Special hazards arising from the substance or mixture**

In the event of a fire, carbon monoxide (CO) and carbon dioxide (CO<sub>2</sub>) can be released.  
In case of fire, keep containers cool with water spray.

**5.3. Advice for firefighters**

Wear self-contained breathing apparatus and full protective clothing, such as turn-out gear.

## SECTION 6: Accidental release measures

**6.1. Personal precautions, protective equipment and emergency procedures**

Ensure adequate ventilation.

**6.3. Methods and material for containment and cleaning up**

For small spills wipe up with paper towel and place in container for disposal.  
For large spills absorb onto inert absorbent material and place in sealed container for disposal.

**6.4. Reference to other sections**

See advice in section 8

## SECTION 7: Handling and storage

**7.1. Precautions for safe handling**

Use only in well-ventilated areas.  
Gloves and safety glasses should be worn  
Prolonged or repeated skin contact should be avoided to minimise any risk of sensitisation.

**Hygiene measures:**

Good industrial hygiene practices should be observed.  
Do not eat, drink or smoke while working.  
Wash hands before work breaks and after finishing work.

**7.2. Conditions for safe storage, including any incompatibilities**

Store in original containers at 8-21°C (46.4-69.8°F) and do not return residual materials to containers as contamination may reduce the shelf life of the bulk product.

**7.3. Specific end use(s)**

Threadlocker

**SECTION 8: Exposure controls/personal protection****8.1. Control parameters****Occupational Exposure Limits**

Valid for  
Great Britain

Ingredient	ppm	mg/m <sup>3</sup>	Type	Category	Remarks
PROPANE-1,2-DIOL, PARTICULATES 57-55-6		10	Time Weighted Average (TWA):		EH40 WEL
PROPANE-1,2-DIOL, TOTAL VAPOUR AND PARTICULATES 57-55-6	150	474	Time Weighted Average (TWA):		EH40 WEL
CUMENE 98-82-8	50	250	Short Term Exposure Limit (STEL):		EH40 WEL
CUMENE 98-82-8			Skin designation:	Can be absorbed through the skin.	EH40 WEL
CUMENE 98-82-8	25	125	Time Weighted Average (TWA):		EH40 WEL
CUMENE 98-82-8	50	250	Short Term Exposure Limit (STEL):	Indicative	ECLTV
CUMENE 98-82-8	20	100	Time Weighted Average (TWA):	Indicative	ECLTV

**Biological Exposure Indices:**

None

**8.2. Exposure controls:****Respiratory protection:**

Use only in well-ventilated areas.

An approved mask or respirator fitted with an organic vapour cartridge should be worn if the product is used in a poorly ventilated area

Filter type: A

**Hand protection:**

Chemical-resistant protective gloves (EN 374).

Suitable materials for short-term contact or splashes (recommended: at least protection index 2, corresponding to > 30 minutes permeation time as per EN 374):

nitrile rubber (NBR;  $\geq 0.4$  mm thickness)

Suitable materials for longer, direct contact (recommended: protection index 6, corresponding to > 480 minutes permeation time as per EN 374):

nitrile rubber (NBR;  $\geq 0.4$  mm thickness)

This information is based on literature references and on information provided by glove manufacturers, or is derived by analogy with similar substances. Please note that in practice the working life of chemical-resistant protective gloves may be considerably shorter than the permeation time determined in accordance with EN 374 as a result of the many influencing factors (e.g. temperature). If signs of wear and tear are noticed then the gloves should be replaced.

**Eye protection:**

Wear protective glasses.

**Skin protection:**

Wear suitable protective clothing.

**SECTION 9: Physical and chemical properties****9.1. Information on basic physical and chemical properties**

Appearance	liquid purple
Odor	characteristic
Odour threshold	No data available / Not applicable
pH ( )	3,00 - 6,00
Initial boiling point	> 150 °C (> 302 °F)
Flash point	> 100 °C (> 212 °F)
Decomposition temperature	No data available / Not applicable
Vapour pressure (25 °C (77 °F))	< 0,1300000 mbar
Density ( )	1,08 g/cm <sup>3</sup>
Bulk density	No data available / Not applicable
Viscosity	No data available / Not applicable
Viscosity (kinematic)	No data available / Not applicable
Explosive properties	No data available / Not applicable
Solubility (qualitative) (Solvent: Water)	Slight
Solubility (qualitative) (Solvent: Acetone)	Miscible
Solidification temperature	No data available / Not applicable
Melting point	No data available / Not applicable
Flammability	No data available / Not applicable
Auto-ignition temperature	No data available / Not applicable
Explosive limits	No data available / Not applicable
Partition coefficient: n-octanol/water	No data available / Not applicable
Evaporation rate	No data available / Not applicable
Vapor density	No data available / Not applicable
Oxidising properties	No data available / Not applicable

**9.2. Other information**

No data available / Not applicable

**SECTION 10: Stability and reactivity****10.1. Reactivity**

Peroxides.

**10.2. Chemical stability**

Stable under recommended storage conditions.

**10.3. Possibility of hazardous reactions**

See section reactivity

**10.4. Conditions to avoid**

Stable under normal conditions of storage and use.

**10.5. Incompatible materials**

None if used properly.

**10.6. Hazardous decomposition products**

Oxides of carbon.

**SECTION 11: Toxicological information****11.1. Information on toxicological effects****General toxicological information:**

The mixture is classified based on the available hazard information for the ingredients as defined in the classification criteria for mixtures for each hazard class or differentiation in Annex I to Regulation 1272/2008/EC. Relevant available health/ecological information for the substances listed under Section 3 is provided in the following.

**Oral toxicity:**

May cause irritation to the digestive tract.

**Inhalative toxicity:**

May cause respiratory irritation.

**Skin irritation:**

Although it is not a common sensitizer there may be a risk of sensitization on prolonged or repeated contact with damaged skin

**Eye irritation:**

Causes serious eye irritation.

**Acute oral toxicity:**

Hazardous components CAS-No.	Value type	Value	Route of application	Exposure time	Species	Method
Cumene hydroperoxide 80-15-9	LD50	550 mg/kg	oral		rat	

**Skin corrosion/irritation:**

Hazardous components CAS-No.	Result	Exposure time	Species	Method
Cumene hydroperoxide 80-15-9	corrosive		rabbit	

**Germ cell mutagenicity:**

Hazardous components CAS-No.	Result	Type of study / Route of administration	Metabolic activation / Exposure time	Species	Method
Cumene hydroperoxide 80-15-9	positive	bacterial reverse mutation assay (e.g Ames test)	without		OECD Guideline 471 (Bacterial Reverse Mutation Assay)
Cumene hydroperoxide 80-15-9	negative	dermal		mouse	

**SECTION 12: Ecological information****General ecological information:**

The mixture is classified based on the available hazard information for the ingredients as defined in the classification criteria for mixtures for each hazard class or differentiation in Annex I to Regulation 1272/2008/EC. Relevant available health/ecological information for the substances listed under Section 3 is provided in the following.

**12.1. Toxicity****Ecotoxicity:**

Do not empty into drains / surface water / ground water.

Hazardous components CAS-No.	Value type	Value	Acute Toxicity Study	Exposure time	Species	Method
Cumene hydroperoxide 80-15-9	LC50	3,9 mg/l	Fish	96 h	Oncorhynchus mykiss	OECD Guideline 203 (Fish, Acute Toxicity Test)
Cumene hydroperoxide 80-15-9	EC50	18 mg/l	Daphnia	48 h	Daphnia magna	OECD Guideline 202 (Daphnia sp. Acute Immobilisation Test)
Cumene hydroperoxide 80-15-9	ErC50	3,1 mg/l	Algae	72 h	Pseudokirchnerella subcapitata	OECD Guideline 201 (Alga, Growth Inhibition Test)
1,4-Naphthalenedione 130-15-4	EC50	0,011 mg/l	Algae	72 h	Dunaliella bioculata	OECD Guideline 201 (Alga, Growth Inhibition Test)

## 12.2. Persistence and degradability

### Persistence and Biodegradability:

No data available for the product.

Hazardous components CAS-No.	Result	Route of application	Degradability	Method
Cumene hydroperoxide 80-15-9		no data	0 %	OECD Guideline 301 B (Ready Biodegradability: CO2 Evolution Test)
1,4-Naphthalenedione 130-15-4		no data	0 - 60 %	

## 12.3. Bioaccumulative potential / 12.4. Mobility in soil

### Mobility:

Cured adhesives are immobile.

Hazardous components CAS-No.	LogKow	Bioconcentration factor (BCF)	Exposure time	Species	Temperature	Method
Cumene hydroperoxide 80-15-9		9,1		calculation		OECD Guideline 305 (Bioconcentration: Flow- through Fish Test)
Cumene hydroperoxide 80-15-9	2,16					
1,4-Naphthalenedione 130-15-4	1,71					

## 12.5. Results of PBT and vPvB assessment

No data available.

## 12.6. Other adverse effects

No data available.

# SECTION 13: Disposal considerations

## 13.1. Waste treatment methods

**Product disposal:**

Dispose of in accordance with local and national regulations.

Contribution of this product to waste is very insignificant in comparison to article in which it is used

**Disposal of uncleaned packages:**

After use, tubes, cartons and bottles containing residual product should be disposed of as chemically contaminated waste in an authorised legal land fill site or incinerated.

Disposal must be made according to official regulations.

**Waste code**

08 04 09 waste adhesives and sealants containing organic solvents and other dangerous substances

## SECTION 14: Transport information

**14.1. UN number**

Not hazardous according to RID, ADR, ADNR, IMDG, IATA-DGR.

**14.2. UN proper shipping name**

Not hazardous according to RID, ADR, ADNR, IMDG, IATA-DGR.

**14.3. Transport hazard class(es)**

Not hazardous according to RID, ADR, ADNR, IMDG, IATA-DGR.

**14.4. Packaging group**

Not hazardous according to RID, ADR, ADNR, IMDG, IATA-DGR.

**14.5. Environmental hazards**

Not hazardous according to RID, ADR, ADNR, IMDG, IATA-DGR.

**14.6. Special precautions for user**

Not hazardous according to RID, ADR, ADNR, IMDG, IATA-DGR.

**14.7. Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code**

not applicable

## SECTION 15: Regulatory information

**15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture**

VOC content < 3 %  
(1999/13/EC)

**15.2. Chemical safety assessment**

A chemical safety assessment has not been carried out.

## SECTION 16: Other information

The labelling of the product is indicated in Section 2. The full text of all abbreviations indicated by codes in this safety data sheet are as follows:

- R10 Flammable.
- R21/22 Harmful in contact with skin and if swallowed.
- R23 Toxic by inhalation.
- R25 Toxic if swallowed.
- R26 Very toxic by inhalation.
- R34 Causes burns.
- R36/37/38 Irritating to eyes, respiratory system and skin.
- R37 Irritating to respiratory system.
- R43 May cause sensitisation by skin contact.
- R48/20/22 Harmful: danger of serious damage to health by prolonged exposure through inhalation and if swallowed.
- R50/53 Very toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.
- R51/53 Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.
- R65 Harmful: may cause lung damage if swallowed.
- R7 May cause fire.
- H242 Heating may cause a fire.
- H301 Toxic if swallowed.
- H302 Harmful if swallowed.
- H312 Harmful in contact with skin.
- H314 Causes severe skin burns and eye damage.
- H315 Causes skin irritation.
- H317 May cause an allergic skin reaction.
- H319 Causes serious eye irritation.
- H330 Fatal if inhaled.
- H331 Toxic if inhaled.
- H335 May cause respiratory irritation.
- H373 May cause damage to organs through prolonged or repeated exposure.
- H400 Very toxic to aquatic life.
- H410 Very toxic to aquatic life with long lasting effects.
- H411 Toxic to aquatic life with long lasting effects.

### Further information:

This information is based on our current level of knowledge and relates to the product in the state in which it is delivered. It is intended to describe our products from the point of view of safety requirements and is not intended to guarantee any particular properties.