


MECHANICAL DETAILS

- Shell Style Model** ECP* : Fixed receptacle with two nuts long threaded shell with straight contact for printed circuit (back panel mounting)
- Keying** Hermaphroditic keying ("half moon" insert), plug has male pin 1
- Housing Material** Brass (chrome plated) shell and collet nut, nickel plated brass latch sleeve and mid pieces
- Cable Fixing** 0 - 0 mm

Variant 2 :

	A	B	E	N	S1	S3	e
Mm.	20	19.5	11	20	13.5	17	M15x1.0
In.	0.79	0.77	0.43	0.79	0.53	0.67	




PERFORMANCE DETAIL

- Insert** 2S.310 : 10 Low Voltage
- Insulator** L: PEEK
- Specifications**
- Contact Type:** Print (straight)
- Max. Matings:** 5000
- Contact Dia.:** 0.9 mm (0.0354in)
- R (max):** 4.8 mOhm



OTHER CHARACTERISTICS







- Endurance (Shell)** Endurance (Shell):
- Temp (min)** -55°C
- Temp (max)** +250°C
- Humidity (max):** <=95% [at 60 deg C /140 F]
- Vibration:** 15 g [10 Hz - 2000 Hz]
- Shock Resistance:** 100 g [6 ms]
- Salt Spray** >144 hr
- Climatical** 50/175/21
- Shielding (min):** 75 dB (10 MHz)
- Shielding (min):** 40 dB (1 GHz)
- IP Rating** 50



Available Download

 [unipole_multipole.pdf](#)

Related links

-  [Contact](#)
-  [Quote Request](#)
-  [Catalogs Downloads](#)
-  [Catalogs Requests](#)
-  [Sample Request](#)
-  [3D drawings](#)