



Safety Data Sheet according to Regulation (EC) No1907/2006

Page 1 of 14

SDS No. : 173280
V005.1

7386 Activator

Revision: 24.04.2014
printing date: 17.12.2014

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

7386 Activator

Contains:

Hydrocarbons, C7, n-alkanes, isoalkanes, cyclics
Diethyl-phenyl-propyl-dihydropyridine

1.2. Relevant identified uses of the substance or mixture and uses advised against

Intended use:
activator

1.3. Details of the supplier of the safety data sheet

Henkel Limited
2 Bishop Square Business Park
AL109EY Herfordshire Hatfield

Great Britain

Phone: +44 1606 593933
Fax-no.: +44 1606 863762

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification (CLP):


Flammable liquids	Category 2
H225 Highly flammable liquid and vapor.	
Acute toxicity	Category 4
H302 Harmful if swallowed.	
Route of Exposure: Oral	
Skin irritation	Category 2
H315 Causes skin irritation.	
Serious eye irritation	Category 2
H319 Causes serious eye irritation.	
Specific target organ toxicity - single exposure	Category 3
H336 May cause drowsiness or dizziness.	
Target organ: Central Nervous System	
Aspiration hazard	Category 1
H304 May be fatal if swallowed and enters airways.	
Chronic hazards to the aquatic environment	Category 2
H411 Toxic to aquatic life with long lasting effects.	

Classification (DPD):




- F - Highly flammable
- R11 Highly flammable.
- Xn - Harmful
- R65 Harmful: may cause lung damage if swallowed.
- R21/22 Harmful in contact with skin and if swallowed.
- N - Dangerous for the environment
- R51/53 Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.
- Xi - Irritant
- R36/38 Irritating to eyes and skin.
- R67 Vapours may cause drowsiness and dizziness.

2.2. Label elements

Label elements (CLP):

Hazard pictogram:	
Signal word:	Danger
Hazard statement:	H225 Highly flammable liquid and vapor. H302 Harmful if swallowed. H304 May be fatal if swallowed and enters airways. H319 Causes serious eye irritation. H315 Causes skin irritation. H336 May cause drowsiness or dizziness. H411 Toxic to aquatic life with long lasting effects.
Precautionary statement:	***For consumer use only: P101 If medical advice is needed, have product container or label at hand. P102 Keep out of reach of children. P501 Dispose of waste and residues in accordance with local authority requirements***
Precautionary statement: Prevention	P210 Keep away from heat/open flames/hot surfaces. - No smoking. P261 Avoid breathing vapours. P273 Avoid release to the environment.
Precautionary statement: Response	P301+P310 IF SWALLOWED: Immediately call a POISON CENTER or doctor. P331 Do NOT induce vomiting. P302+P352 IF ON SKIN: Wash with plenty of soap and water. P337+P313 If eye irritation persists: Get medical advice/attention.

Label elements (DPD):

F - Highly flammable	Xn - Harmful	N - Dangerous for the environment
		

Risk phrases:

R11 Highly flammable.
R21/22 Harmful in contact with skin and if swallowed.
R36/38 Irritating to eyes and skin.
R51/53 Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.
R65 Harmful: may cause lung damage if swallowed.
R67 Vapours may cause drowsiness and dizziness.

Safety phrases:

S16 Keep away from sources of ignition - No smoking.
S23 Do not breathe vapour.
S26 In case of contact with eyes, rinse immediately with plenty of water and seek medical advice.
S28 After contact with skin, wash immediately with plenty of water and soap.
S61 Avoid release to the environment. Refer to special instructions/Safety data sheets.
S62 If swallowed, do not induce vomiting: seek medical advice immediately and show this container or label.

Additional labeling:

For consumer use only: S2 Keep out of the reach of children.
S46 If swallowed, seek medical advice immediately and show this container or label.

Contains:

Hydrocarbons, C7, n-alkanes, isoalkanes, cyclics,
Diethyl-phenyl-propyl-dihydropyridine

2.3. Other hazards

None if used properly.

SECTION 3: Composition/information on ingredients

General chemical description:

Solvent based activator.

Declaration of the ingredients according to CLP (EC) No 1272/2008:

Hazardous components CAS-No.	EC Number REACH-Reg No.	content	Classification
Hydrocarbons, C7, n-alkanes, isoalkanes, cyclics 93924-37-9	300-230-4 01-2119475515-33	50- < 75 %	Aspiration hazard 1 H304 Skin irritation 2 H315 Flammable liquids 2 H225 Specific target organ toxicity - single exposure 3; Inhalation H336 Chronic hazards to the aquatic environment 2 H411
Diethyl-phenyl-propyl-dihydropyridine 34562-31-7	252-091-3	25- < 50 %	Acute toxicity 4; Oral H302 Acute toxicity 4; Dermal H312 Skin irritation 2; Dermal H315 Serious eye irritation 2 H319 Chronic hazards to the aquatic environment 4 H413
Propan-2-ol 67-63-0	200-661-7 01-2119457558-25	10- < 20 %	Flammable liquids 2 H225 Serious eye irritation 2 H319 Specific target organ toxicity - single exposure 3 H336

For full text of the H - statements and other abbreviations see section 16 "Other information".
Substances without classification may have community workplace exposure limits available.

Declaration of ingredients according to DPD (EC) No 1999/45:

Hazardous components CAS-No.	EC Number REACH-Reg No.	content	Classification
Hydrocarbons, C7, n-alkanes, isoalkanes, cyclics 93924-37-9	300-230-4 01-2119475515-33	50 - < 75 %	Xn - Harmful; R65 Xi - Irritant; R38 F - Highly flammable; R11 R67 N - Dangerous for the environment; R51/53
Diethyl-phenyl-propyl-dihydropyridine 34562-31-7	252-091-3	25 - < 50 %	Xn - Harmful; R21/22 Xi - Irritant; R36/38 R53
Propan-2-ol 67-63-0	200-661-7 01-2119457558-25	10 - < 20 %	F - Highly flammable; R11 Xi - Irritant; R36 R67

For full text of the R-Phrases indicated by codes see section 16 'Other Information'.
Substances without classification may have community workplace exposure limits available.

SECTION 4: First aid measures**4.1. Description of first aid measures****Inhalation:**

Move to fresh air.
Seek medical advice.

Skin contact:

Rinse with running water and soap.
Seek medical advice.

Eye contact:

Rinse immediately with plenty of running water (for 10 minutes). Seek medical attention if necessary.

Ingestion:

Rinse mouth, drink 1-2 glasses of water, do not induce vomiting, consult a doctor.

4.2. Most important symptoms and effects, both acute and delayed

ASPIRATION: Coughing, shortness of breath, nausea. Delayed effect: bronchopneumonia or pulmonary oedema

EYE: Irritation, conjunctivitis.

SKIN: Redness, inflammation.

INGESTION: Nausea, vomiting, diarrhoea, abdominal pain.

Vapors may cause drowsiness and dizziness.

4.3. Indication of any immediate medical attention and special treatment needed

Swallowing may cause irritation of mouth, throat and digestive tract, diarrhoea and vomiting

Do not induce vomiting.

Seek medical attention from a specialist.

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable extinguishing media:

Foam, extinguishing powder, carbon dioxide.

Extinguishing media which must not be used for safety reasons:

Water

5.2. Special hazards arising from the substance or mixture

Vapours may accumulate in low or confined areas, travel considerable distance to source of ignition, and flash back.

Oxides of carbon, oxides of nitrogen, irritating organic vapors.

5.3. Advice for firefighters

Wear self-contained breathing apparatus.

Additional information:

In case of fire, keep containers cool with water spray.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Remove sources of ignition.

Ensure adequate ventilation.

6.2. Environmental precautions

Do not let product enter drains.

6.3. Methods and material for containment and cleaning up

Wipe up using absorbent material.

Store in a partly filled, closed container until disposal.

Dispose of contaminated material as waste according to Section 13.

6.4. Reference to other sections

See advice in section 8

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Keep away from sources of ignition - no smoking.

Vapours should be extracted to avoid inhalation.

Use only in well-ventilated areas.

Hygiene measures:

- Wash hands before work breaks and after finishing work.
- Do not eat, drink or smoke while working.
- Good industrial hygiene practices should be observed.

7.2. Conditions for safe storage, including any incompatibilities

- Store in a cool, dry place.
- Do not store near sources of heat or ignition, or reactive materials.

7.3. Specific end use(s)

activator

SECTION 8: Exposure controls/personal protection**8.1. Control parameters****Occupational Exposure Limits**

Valid for
Great Britain

Ingredient	ppm	mg/m ³	Type	Category	Remarks
PROPAN-2-OL 67-63-0	500	1.250	Short Term Exposure Limit (STEL):		EH40 WEL
PROPAN-2-OL 67-63-0	400	999	Time Weighted Average (TWA):		EH40 WEL

Predicted No-Effect Concentration (PNEC):

Name on list	Environmental Compartment	Exposure period	Value				Remarks
			mg/l	ppm	mg/kg	others	
Propan-2-ol 67-63-0	aqua (freshwater)					140,9 mg/L	
Propan-2-ol 67-63-0	aqua (marine water)					140,9 mg/L	
Propan-2-ol 67-63-0	sediment (freshwater)				552 mg/kg		
Propan-2-ol 67-63-0	sediment (marine water)				552 mg/kg		
Propan-2-ol 67-63-0	soil				28 mg/kg		
Propan-2-ol 67-63-0	aqua (intermittent releases)					140,9 mg/L	
Propan-2-ol 67-63-0	STP					2251 mg/L	
Propan-2-ol 67-63-0	oral					160 mg/kg food	

Derived No-Effect Level (DNEL):

Name on list	Application Area	Route of Exposure	Health Effect	Exposure Time	Value	Remarks
Hydrocarbons, C7, n-alkanes, isoalkanes, cyclics 93924-37-9	worker	Dermal	Long term exposure - systemic effects		300 mg/kg bw/day	
Hydrocarbons, C7, n-alkanes, isoalkanes, cyclics 93924-37-9	worker	inhalation	Long term exposure - systemic effects		2085 mg/m ³	
Hydrocarbons, C7, n-alkanes, isoalkanes, cyclics 93924-37-9	general population	Dermal	Long term exposure - systemic effects		149 mg/kg bw/day	
Hydrocarbons, C7, n-alkanes, isoalkanes, cyclics 93924-37-9	general population	oral	Long term exposure - systemic effects		149 mg/kg bw/day	
Hydrocarbons, C7, n-alkanes, isoalkanes, cyclics 93924-37-9	general population	inhalation	Long term exposure - systemic effects		477 mg/m ³	
Propan-2-ol 67-63-0	worker	Dermal	Long term exposure - systemic effects		888 mg/kg bw/day	
Propan-2-ol 67-63-0	worker	inhalation	Long term exposure - systemic effects		500 mg/m ³	
Propan-2-ol 67-63-0	general population	Dermal	Long term exposure - systemic effects		319 mg/kg bw/day	
Propan-2-ol 67-63-0	general population	inhalation	Long term exposure - systemic effects		89 mg/m ³	
Propan-2-ol 67-63-0	general population	oral	Long term exposure - systemic effects		26 mg/kg bw/day	

Biological Exposure Indices:

None

8.2. Exposure controls:

Respiratory protection:

Do not inhale vapors and fumes.

Use only in well-ventilated areas.

An approved mask or respirator fitted with an organic vapour cartridge should be worn if the product is used in a poorly ventilated area

Filter type: A

Hand protection:

Chemical-resistant protective gloves (EN 374).

Suitable materials for short-term contact or splashes (recommended: at least protection index 2, corresponding to > 30 minutes permeation time as per EN 374):

nitrile rubber (NBR; ≥ 0.4 mm thickness)

Suitable materials for longer, direct contact (recommended: protection index 6, corresponding to > 480 minutes permeation time as per EN 374):

nitrile rubber (NBR; ≥ 0.4 mm thickness)

This information is based on literature references and on information provided by glove manufacturers, or is derived by analogy with similar substances. Please note that in practice the working life of chemical-resistant protective gloves may be considerably shorter than the permeation time determined in accordance with EN 374 as a result of the many influencing factors (e.g. temperature). If signs of wear and tear are noticed then the gloves should be replaced.

Eye protection:

Wear protective glasses.

Skin protection:

Suitable protective clothing

SECTION 9: Physical and chemical properties**9.1. Information on basic physical and chemical properties**

Appearance	liquid clear yellow, Amber, greenish
Odor	Aliphatic
Odour threshold	No data available / Not applicable
pH	not applicable
Initial boiling point	82 °C (179.6 °F)
Flash point	< 0 °C (< 32 °F)
Decomposition temperature	No data available / Not applicable
Vapour pressure (20 °C (68 °F))	35 mm hg
Density ()	0,8 g/cm3
Bulk density	No data available / Not applicable
Viscosity	No data available / Not applicable
Viscosity (kinematic)	No data available / Not applicable
Explosive properties	No data available / Not applicable
Solubility (qualitative)	Insoluble
Solidification temperature	No data available / Not applicable
Melting point	No data available / Not applicable
Flammability	No data available / Not applicable
Auto-ignition temperature	No data available / Not applicable
Explosive limits	No data available / Not applicable
Partition coefficient: n-octanol/water	No data available / Not applicable
Evaporation rate	No data available / Not applicable
Vapor density	Heavier than air
Oxidising properties	No data available / Not applicable

9.2. Other information

No data available / Not applicable

SECTION 10: Stability and reactivity**10.1. Reactivity**

Strong oxidizing agents.

10.2. Chemical stability

Stable under recommended storage conditions.

10.3. Possibility of hazardous reactions

See section reactivity

10.4. Conditions to avoidNo decomposition if used according to specifications.
Heat, flames, sparks and other sources of ignition.**10.5. Incompatible materials**

None if used properly.

10.6. Hazardous decomposition products

None if used for intended purpose.

SECTION 11: Toxicological information**11.1. Information on toxicological effects****General toxicological information:**

The mixture is classified based on the available hazard information for the ingredients as defined in the classification criteria for mixtures for each hazard class or differentiation in Annex I to Regulation 1272/2008/EC. Relevant available health/ecological information for the substances listed under Section 3 is provided in the following.

Oral toxicity:

Harmful if swallowed.
May be fatal if swallowed and enters airways.

Inhalative toxicity:

May cause headache and dizziness.

Skin irritation:

Causes skin irritation.
Solvent may remove essential oils from the skin making it susceptible to attack from other chemicals.

Eye irritation:

Causes serious eye irritation.

Acute oral toxicity:

Hazardous components CAS-No.	Value type	Value	Route of application	Exposure time	Species	Method
Hydrocarbons, C7, n-alkanes, isoalkanes, cyclics 93924-37-9	LD50		oral		rat	OECD Guideline 401 (Acute Oral Toxicity)
Propan-2-ol 67-63-0	LD50	5.338 mg/kg	oral		rat	

Acute inhalative toxicity:

Hazardous components CAS-No.	Value type	Value	Route of application	Exposure time	Species	Method
Hydrocarbons, C7, n-alkanes, isoalkanes, cyclics 93924-37-9	LC50	> 23,3 mg/l	inhalation		rat	OECD Guideline 403 (Acute Inhalation Toxicity)
Propan-2-ol 67-63-0	LC50	72,6 mg/l	inhalation	4 h	rat	

Acute dermal toxicity:

Hazardous components CAS-No.	Value type	Value	Route of application	Exposure time	Species	Method
Hydrocarbons, C7, n-alkanes, isoalkanes, cyclics 93924-37-9	LD50	> 2.920 mg/kg	dermal		rat	OECD Guideline 402 (Acute Dermal Toxicity)
Propan-2-ol 67-63-0	LD50	12.870 mg/kg	dermal		rabbit	

Skin corrosion/irritation:

Hazardous components CAS-No.	Result	Exposure time	Species	Method
Diethyl-phenyl-propyl-dihydropyridine 34562-31-7	irritating			
Propan-2-ol 67-63-0	slightly irritating	4 h	rabbit	OECD Guideline 404 (Acute Dermal Irritation / Corrosion)

Serious eye damage/irritation:

Hazardous components CAS-No.	Result	Exposure time	Species	Method
Diethyl-phenyl-propyl- dihydropyridine 34562-31-7	irritating			
Propan-2-ol 67-63-0	moderately irritating		rabbit	OECD Guideline 405 (Acute Eye Irritation / Corrosion)

Respiratory or skin sensitization:

Hazardous components CAS-No.	Result	Test type	Species	Method
Propan-2-ol 67-63-0	not sensitising	Buehler test	guinea pig	

Germ cell mutagenicity:

Hazardous components CAS-No.	Result	Type of study / Route of administration	Metabolic activation / Exposure time	Species	Method
Propan-2-ol 67-63-0	negative	bacterial reverse mutation assay (e.g Ames test)	with and without		

Repeated dose toxicity

Hazardous components CAS-No.	Result	Route of application	Exposure time / Frequency of treatment	Species	Method
Propan-2-ol 67-63-0	NOAEL=1500	inhalation	13 weeks 6 hours/day, 5 days/week	mouse	

SECTION 12: Ecological information**General ecological information:**

The mixture is classified based on the available hazard information for the ingredients as defined in the classification criteria for mixtures for each hazard class or differentiation in Annex I to Regulation 1272/2008/EC. Relevant available health/ecological information for the substances listed under Section 3 is provided in the following.

12.1. Toxicity**Ecotoxicity:**

Toxic to aquatic life with long lasting effects.
Do not empty into drains / surface water / ground water.

Hazardous components CAS-No.	Value type	Value	Acute Toxicity Study	Exposure time	Species	Method
Hydrocarbons, C7, n-alkanes, isoalkanes, cyclics 93924-37-9	EC50	3 mg/l	Daphnia	48 h	Daphnia magna	OECD Guideline 202 (Daphnia sp. Acute Immobilisation Test)
Hydrocarbons, C7, n-alkanes, isoalkanes, cyclics 93924-37-9	NOEC	0,17 mg/l	chronic Daphnia	21 d	Daphnia magna	OECD 211 (Daphnia magna, Reproduction Test)
Propan-2-ol 67-63-0	LC50	9.640 mg/l	Fish	96 h	Pimephales promelas	OECD Guideline 203 (Fish, Acute Toxicity Test)
Propan-2-ol 67-63-0	EC50	13.299 mg/l	Daphnia	48 h	Daphnia magna	OECD Guideline 202 (Daphnia sp. Acute Immobilisation Test)
Propan-2-ol 67-63-0	EC50	> 1.000 mg/l	Algae	96 h	Scenedesmus subspicatus (new name: Desmodesmus subspicatus)	OECD Guideline 201 (Alga, Growth Inhibition Test)
	NOEC	1.000 mg/l	Algae	96 h	Scenedesmus subspicatus (new name: Desmodesmus subspicatus)	OECD Guideline 201 (Alga, Growth Inhibition Test)
Propan-2-ol 67-63-0	NOEC	30 mg/l	chronic Daphnia	21 d	Daphnia magna	OECD 211 (Daphnia magna, Reproduction Test)

12.2. Persistence and degradability

Persistence and Biodegradability:

No data available.

Hazardous components CAS-No.	Result	Route of application	Degradability	Method
Hydrocarbons, C7, n-alkanes, isoalkanes, cyclics 93924-37-9	readily biodegradable	aerobic	98 %	OECD Guideline 301 F (Ready Biodegradability: Manometric Respirometry Test)
Propan-2-ol 67-63-0	readily biodegradable	aerobic	70 - 84 %	EU Method C.4-E (Determination of the "Ready" Biodegradability Closed Bottle Test)

12.3. Bioaccumulative potential / 12.4. Mobility in soil

Mobility:

The product evaporates readily.

Bioaccumulative potential:

No data available.

Hazardous components CAS-No.	LogKow	Bioconcentration factor (BCF)	Exposure time	Species	Temperature	Method
Propan-2-ol 67-63-0	0,05					OECD Guideline 107 (Partition Coefficient (n- octanol / water), Shake Flask Method)

12.5. Results of PBT and vPvB assessment

Hazardous components CAS-No.	PBT/vPvB

Hydrocarbons, C7, n-alkanes, isoalkanes, cyclics 93924-37-9	Not fulfilling Persistent, Bioaccumulative and Toxic (PBT), very Persistent and very Bioaccumulative (vPvB) criteria.
Propan-2-ol 67-63-0	Not fulfilling Persistent, Bioaccumulative and Toxic (PBT), very Persistent and very Bioaccumulative (vPvB) criteria.

12.6. Other adverse effects

No data available.

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Product disposal:

Dispose of according to regulations.

Disposal of uncleaned packages:

After use, tubes, cartons and bottles containing residual product should be disposed of as chemically contaminated waste in an authorised legal land fill site or incinerated.

Disposal must be made according to official regulations.

Waste code

14 06 03 - other solvents and solvent mixtures

SECTION 14: Transport information**14.1. UN number**

ADR	1993
RID	1993
ADNR	1993
IMDG	1993
IATA	1993

14.2. UN proper shipping name

ADR	FLAMMABLE LIQUID, N.O.S. (Heptanes,Isopropanol)
RID	FLAMMABLE LIQUID, N.O.S. (Heptanes,Isopropanol)
ADNR	FLAMMABLE LIQUID, N.O.S. (Heptanes,Isopropanol)
IMDG	FLAMMABLE LIQUID, N.O.S. (Heptanes,Isopropanol)
IATA	Flammable liquid, n.o.s. (Heptanes,Isopropanol)

14.3. Transport hazard class(es)

ADR	3
RID	3
ADNR	3
IMDG	3
IATA	3

14.4. Packaging group

ADR	II
RID	II
ADNR	II
IMDG	II
IATA	II

14.5. Environmental hazards

ADR	Environmentally Hazardous
RID	Environmentally Hazardous
ADNR	Environmentally Hazardous
IMDG	Environmentally Hazardous
IATA	not applicable

14.6. Special precautions for user

ADR	Special provision 640D Tunnelcode: (D/E)
RID	Special provision 640D
ADNR	Special provision 640D
IMDG	not applicable
IATA	not applicable

14.7. Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code

not applicable

SECTION 15: Regulatory information**15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture**VOC content 100 %
(1999/13/EC)**15.2. Chemical safety assessment**

A chemical safety assessment has not been carried out.

SECTION 16: Other information

The labelling of the product is indicated in Section 2. The full text of all abbreviations indicated by codes in this safety data sheet are as follows:

- R11 Highly flammable.
- R21/22 Harmful in contact with skin and if swallowed.
- R36 Irritating to eyes.
- R36/38 Irritating to eyes and skin.
- R38 Irritating to skin.
- R51/53 Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.
- R53 May cause long-term adverse effects in the aquatic environment.
- R65 Harmful: may cause lung damage if swallowed.
- R67 Vapours may cause drowsiness and dizziness.
- H225 Highly flammable liquid and vapor.
- H302 Harmful if swallowed.
- H304 May be fatal if swallowed and enters airways.
- H312 Harmful in contact with skin.
- H315 Causes skin irritation.
- H319 Causes serious eye irritation.
- H336 May cause drowsiness or dizziness.
- H411 Toxic to aquatic life with long lasting effects.
- H413 May cause long lasting harmful effects to aquatic life.

Further information:

This information is based on our current level of knowledge and relates to the product in the state in which it is delivered. It is intended to describe our products from the point of view of safety requirements and is not intended to guarantee any particular properties.