

tesa® 51608

PET fleece wire harness tape for the passenger compartment

PRODUCT INFORMATION

Product Description

tesa® 51608 is the universal tape for wire harness bundling in the passenger compartment. It combines features such as noise damping, abrasion resistance and bundling strength while keeping harnesses flexible enabling an easy harness assembly process at the OEM. tesa® 51608 is for manual application.

Features:

- noise damping
- abrasion resistant
- flexible and smooth
- tear resistant
- stable unwind force
- resistant to ageing
- strong adhesion
- handtearable

Main Application

Wire Harnessing

Technical Data

■ Backing material	PET fleece	■ Temperature resistance (3000h)	105 °C
■ Total thickness	280 µm	■ Abrasion resistance (10mm mandrel)	Class B (acc. to LV312)
■ Type of adhesive	rubber based	■ Abrasion resistance (5mm mandrel)	Class A (acc. to LV312)
■ Adhesion to steel	3 N/cm	■ Flame resistance as composite	Class B (acc. to LV312)
■ Elongation at break	20 %	■ Unwind force (roll width ≤ 9mm)	4.6 N/roll (30 m/min)
■ Tensile strength	40 N/cm	■ Unwind force (roll width > 9mm)	9 N/roll (30 m/min)
■ Temperature Resistance MIN	-40 °C	■ Noise damping (decibel)	Class C (acc. to LV312)

For latest information on this product please visit <http://l.tesa.com/?ip=51608>

Page 1 of 1 / As of 09/20/14

tesa UK Ltd.

Yeomans Drive, Blakelands
Milton Keynes, Bucks MK 14 5LS
Phone: +44 (1) 908 211 333
Fax: +44 (1) 908 211 555
ukenquiry@tesa.com
www.tesa.co.uk