

SAFETY DATA SHEET SAFEWASH TOTAL-CONCENTRATE

SECTION 1: IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

1.1. Product identifier

Product name SAFEWASH TOTAL-CONCENTRATE
Product No. SWAT, ESWAT01L, ESWAT05L, ZE

1.2. Relevant identified uses of the substance or mixture and uses advised against

Identified uses Cleaning Product
Uses advised against At this moment in time we do not have information on use restrictions. They will be included in this safety data sheet when available

1.3. Details of the supplier of the safety data sheet

Supplier ELECTROLUBE. A division of HK
WENTWORTH LTD
ASHBY PARK, COALFIELD WAY,
ASHBY DE LA ZOUCH, LEICESTERSHIRE
LE65 1JR
UNITED KINGDOM
+44 (0)1530 419600
+44 (0)1530 416640
info@hkw.co.uk

1.4. Emergency telephone number

+44 (0)1530 419600 between 8.30am - 5.00pm GMT Mon – Fri

SECTION 2: HAZARDS IDENTIFICATION

2.1. Classification of the substance or mixture

Classification (EC 1272/2008)

Physical and Chemical Hazards	Not classified.
Human health	Skin Irrit. 2 - H315; Eye Irrit. 2 - H319
Environment	Not classified.

Classification (1999/45/EEC)

Xi; R36/38.

The Full Text for all R-Phrases and Hazard Statements are Displayed in Section 16.

2.2. Label elements

Label In Accordance With (EC) No. 1272/2008



Signal Word

Warning

Hazard Statements

H315	Causes skin irritation.
H319	Causes serious eye irritation.

Precautionary Statements

P280	Wear protective gloves, eye and face protection.
P305+351+338	IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.

SAFEWASH TOTAL-CONCENTRATE

P313
P302+352

Get medical advice/attention.
IF ON SKIN: Wash with plenty of soap and water.

2.3. Other hazards

Not Classified as PBT/vPvB by current EU criteria.

SECTION 3: COMPOSITION/INFORMATION ON INGREDIENTS

3.2. Mixtures

2-AMINO-2-METHYLPROPANOL	10-30%
CAS-No.: 124-68-5	EC No.: 204-709-8
Classification (EC 1272/2008) Skin Irrit. 2 - H315 Eye Irrit. 2 - H319 Aquatic Chronic 3 - H412	Classification (67/548/EEC) Xi;R36/38 R52/53
3-BUTOXYPROPAN-2-OL	5-10%
CAS-No.: 5131-66-8	EC No.: 225-878-4
Classification (EC 1272/2008) Skin Irrit. 2 - H315 Eye Irrit. 2 - H319	Classification (67/548/EEC) Xi;R36/38
DIPROPYLENE GLYCOL MONOMETHYL ETHER	1-5%
CAS-No.: 34590-94-8	EC No.:
Classification (EC 1272/2008) Not classified.	Classification (67/548/EEC) Not classified.

The Full Text for all R-Phrases and Hazard Statements are Displayed in Section 16.

Composition Comments

Ingredients not listed are classified as non-hazardous or at a concentration below reportable levels.

SECTION 4: FIRST AID MEASURES

4.1. Description of first aid measures

Inhalation

Move the exposed person to fresh air at once. Rinse nose and mouth with water. Get medical attention if any discomfort continues.

Ingestion

Rinse mouth thoroughly. Drink plenty of water. Get medical attention.

Skin contact

Wash the skin immediately with soap and water. Get medical attention if irritation persists after washing.

Eye contact

Make sure to remove any contact lenses from the eyes before rinsing. Promptly wash eyes with plenty of water while lifting the eye lids. Continue to rinse for at least 15 minutes. Get medical attention if any discomfort continues.

4.2. Most important symptoms and effects, both acute and delayed

4.3. Indication of any immediate medical attention and special treatment needed

Treat Symptomatically.

SECTION 5: FIREFIGHTING MEASURES

SAFEWASH TOTAL-CONCENTRATE

5.1. Extinguishing media

Extinguishing media

This product is not flammable. Use fire-extinguishing media appropriate for surrounding materials.

5.2. Special hazards arising from the substance or mixture

Hazardous combustion products

Thermal decomposition or combustion may liberate carbon oxides and other toxic gases or vapours.

Unusual Fire & Explosion Hazards

No unusual fire or explosion hazards noted.

5.3. Advice for firefighters

Special Fire Fighting Procedures

No specific fire fighting procedure given.

Protective equipment for fire-fighters

Self contained breathing apparatus and full protective clothing must be worn in case of fire.

SECTION 6: ACCIDENTAL RELEASE MEASURES

6.1. Personal precautions, protective equipment and emergency procedures

Wear protective clothing as described in Section 8 of this safety data sheet.

6.2. Environmental precautions

Do not discharge into drains, water courses or onto the ground.

6.3. Methods and material for containment and cleaning up

Wear necessary protective equipment. Absorb in vermiculite, dry sand or earth and place into containers.

6.4. Reference to other sections

Wear protective clothing as described in Section 8 of this safety data sheet. See section 11 for additional information on health hazards. For waste disposal, see section 13.

SECTION 7: HANDLING AND STORAGE

7.1. Precautions for safe handling

Avoid spilling, skin and eye contact.

7.2. Conditions for safe storage, including any incompatibilities

Store in tightly closed original container in a dry, cool and well-ventilated place. Keep in original container.

7.3. Specific end use(s)

The identified uses for this product are detailed in Section 1.2.

SECTION 8: EXPOSURE CONTROLS/PERSONAL PROTECTION

8.1. Control parameters

Name	STD	TWA - 8 Hrs		STEL - 15 Min		Notes
3-BUTOXYPROPAN-2-OL	SUP	50 ppm				
DIPROPYLENE GLYCOL MONOMETHYL ETHER	WEL	50 ppm	308 mg/m ³			Sk

WEL = Workplace Exposure Limit.

Sk = Can be absorbed through skin.

8.2. Exposure controls

Protective equipment

SAFEWASH TOTAL-CONCENTRATE



Process conditions

Use engineering controls to reduce air contamination to permissible exposure level. Provide eyewash station.

Engineering measures

Provide adequate ventilation, including appropriate local extraction, to ensure that the defined occupational exposure limit is not exceeded.

Respiratory equipment

In case of inadequate ventilation and work of brief duration, use suitable respiratory equipment. Use respiratory equipment with combination filter, type A2/P3. EN14387

Hand protection

Protective gloves must be used if there is a risk of direct contact or splash. The most suitable glove must be chosen in consultation with the gloves supplier, who can inform about the breakthrough time of the glove material. Nitrile gloves are recommended. Gloves should conform to EN374

Eye protection

Use approved safety goggles or face shield. EN166

Other Protection

Wear appropriate clothing to prevent any possibility of skin contact.

Hygiene measures

DO NOT SMOKE IN WORK AREA! Wash hands at the end of each work shift and before eating, smoking and using the toilet. Wash promptly if skin becomes wet or contaminated. When using do not eat, drink or smoke.

SECTION 9: PHYSICAL AND CHEMICAL PROPERTIES

9.1. Information on basic physical and chemical properties

Appearance	Liquid
Colour	Colourless.
Odour	Amine.
Solubility	Soluble in water.
Bulk Density	0.93 @ 20°C (68 F)
pH-Value, Conc. Solution	11-12

9.2. Other information

SECTION 10: STABILITY AND REACTIVITY

10.1. Reactivity

There are no known reactivity hazards associated with this product.

10.2. Chemical stability

Stable under normal temperature conditions.

10.3. Possibility of hazardous reactions

Not determined.

Hazardous Polymerisation

Will not polymerise.

10.4. Conditions to avoid

Avoid contact with acids.

10.5. Incompatible materials

Materials To Avoid

Strong oxidising substances.

10.6. Hazardous decomposition products

Thermal decomposition or combustion may liberate carbon oxides and other toxic gases or vapours.

SECTION 11: TOXICOLOGICAL INFORMATION

SAFEWASH TOTAL-CONCENTRATE

11.1. Information on toxicological effects

Inhalation

May cause irritation to the respiratory system.

Ingestion

May cause burns in mucous membranes, throat, oesophagus and stomach. May cause stomach pain or vomiting.

Skin contact

Irritating to skin. May cause sensitisation by skin contact. Prolonged or repeated exposure may cause severe irritation.

Eye contact

May cause severe irritation to eyes.

Toxicological information on ingredients.

3-BUTOXYPROPAN-2-OL (CAS: 5131-66-8)

Toxic Dose 1 - LD 50

2612-5500 mg/kg (oral rat)

2-AMINO-2-METHYLPROPANOL (CAS: 124-68-5)

Toxic Dose 1 - LD 50

>2900 mg/kg (oral rat)

DIPROPYLENE GLYCOL MONOMETHYL ETHER (CAS: 34590-94-8)

Toxic Dose 1 - LD 50

>5000 mg/kg (oral rat)

Toxic Conc. - LC 50

55 mg/l/4h (inh-rat)

SECTION 12: ECOLOGICAL INFORMATION

Ecotoxicity

Not regarded as dangerous for the environment.

12.1. Toxicity

Ecological information on ingredients.

3-BUTOXYPROPAN-2-OL (CAS: 5131-66-8)

LC 50, 96 Hrs, Fish mg/l

560-1000

EC 50, 48 Hrs, Daphnia, mg/l

>1000

2-AMINO-2-METHYLPROPANOL (CAS: 124-68-5)

LC 50, 96 Hrs, Fish mg/l

190

EC 50, 48 Hrs, Daphnia, mg/l

193

IC 50, 72 Hrs, Algae, mg/l

520

DIPROPYLENE GLYCOL MONOMETHYL ETHER (CAS: 34590-94-8)

LC 50, 96 Hrs, Fish mg/l

>1000

EC 50, 48 Hrs, Daphnia, mg/l

1919

12.2. Persistence and degradability

Degradability

There are no data on the degradability of this product.

Ecological information on ingredients.

2-AMINO-2-METHYLPROPANOL (CAS: 124-68-5)

Degradability

The product is not readily biodegradable.

SAFEWASH TOTAL-CONCENTRATE

12.3. Bioaccumulative potential

Bioaccumulative potential

No data available on bioaccumulation.

12.4. Mobility in soil

12.5. Results of PBT and vPvB assessment

This product does not contain any PBT or vPvB substances.

12.6. Other adverse effects

SECTION 13: DISPOSAL CONSIDERATIONS

General information

Waste is classified as hazardous waste. Disposal to licensed waste disposal site in accordance with the local Waste Disposal Authority.

13.1. Waste treatment methods

Dispose of waste and residues in accordance with local authority requirements.

SECTION 14: TRANSPORT INFORMATION

General

The product is not covered by international regulation on the transport of dangerous goods (IMDG, IATA, ADR/RID).

Road Transport Notes

Not Classified

Rail Transport Notes

Not classified.

Sea Transport Notes

Not classified.

Air Transport Notes

Not classified.

14.1. UN number

14.2. UN proper shipping name

14.3. Transport hazard class(es)

Transport Labels

No transport warning sign required.

14.4. Packing group

14.5. Environmental hazards

Environmentally Hazardous Substance/Marine Pollutant

No.

14.6. Special precautions for user

14.7. Transport in bulk according to Annex II of MARPOL73/78 and the IBC Code

No information required.

SECTION 15: REGULATORY INFORMATION

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

Statutory Instruments

The Chemicals (Hazard Information and Packaging for Supply) Regulations 2009 (S.I 2009 No. 716). Control of Substances Hazardous to Health.

Guidance Notes

Workplace Exposure Limits EH40.

SAFEWASH TOTAL-CONCENTRATE

EU Legislation

Commission Directive 2000/39/EC of 8 June 2000 establishing a first list of indicative occupational exposure limit values in implementation of Council Directive 98/24/EC on the protection of the health and safety of workers from the risks related to chemical agents at work.

Regulation (EC) No 1907/2006 of the European Parliament and of the Council of 18 December 2006 concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals (REACH), establishing a European Chemicals Agency, amending Directive 1999/45/EC and repealing Council Regulation (EEC) No 793/93 and Commission Regulation (EC) No 1488/94 as well as Council Directive 76/769/EEC and Commission Directives 91/155/EEC, 93/67/EEC, 93/105/EC and 2000/21/EC, including amendments.

Regulation (EC) No 1272/2008 of the European Parliament and of the Council of 16 December 2008 on classification, labelling and packaging of substances and mixtures, amending and repealing Directives 67/548/EEC and 1999/45/EC, and amending Regulation (EC) No 1907/2006 with amendments.

Authorisations (Title VII Regulation 1907/2006)

No specific authorisations are noted for this product.

Restrictions (Title VIII Regulation 1907/2006)

No specific restrictions of use are noted for this product.

15.2. Chemical Safety Assessment

No chemical safety assessment has been carried out.

SECTION 16: OTHER INFORMATION

Issued By Helen O'Reilly

Revision Date APRIL 2013

Revision 2

SDS No. 12798

Risk Phrases In Full

R52/53 Harmful to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

R36/38 Irritating to eyes and skin.

NC Not classified.

Hazard Statements In Full

H315 Causes skin irritation.

H319 Causes serious eye irritation.

H412 Harmful to aquatic life with long lasting effects.

Disclaimer

This information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process. Such information is, to the best of the company's knowledge and belief, accurate and reliable as of the date indicated. However, no warranty guarantee or representation is made to its accuracy, reliability or completeness. It is the user's responsibility to satisfy himself as to the suitability of such information for his own particular use.