



Safety Data Sheet according to Regulation (EC) No1907/2006

Page 1 of 8

SUPERLUBE OIL 7GM

SDS No. : 168448
V003.3

Revision: 21.07.2014
printing date: 18.12.2014

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

SUPERLUBE OIL 7GM

1.2. Relevant identified uses of the substance or mixture and uses advised against

Intended use:
Lubricating Oils

1.3. Details of the supplier of the safety data sheet

Henkel Limited
2 Bishop Square Business Park
AL109EY Herfordshire Hatfield

Great Britain

Phone: +44 1606 593933
Fax-no.: +44 1606 863762

ua-productsafety.uk@uk.henkel.com

1.4. Emergency telephone number

24 Hours Emergency Tel: +44 (0)1442 278497

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification (CLP):

||| The substance or mixture is not hazardous according to Regulation (EC) No 1272/2008 (CLP).

Classification (DPD):

The product is not subject to classification according to the calculation methods of the "General Classification Guideline for Preparations of the EC" as issued in the last version.

2.2. Label elements

Label elements (CLP):

||| The substance or mixture is not hazardous according to Regulation (EC) No 1272/2008 (CLP).

||| Supplemental information EUH210 Safety data sheet available on request.

Label elements (DPD):

The product is not subject to classification according to the calculation methods of the "General Classification Guideline for Preparations of the EC" as issued in the last version.

Additional labeling:

Safety data sheet available for professional user on request.

2.3. Other hazards

None if used properly.

SECTION 3: Composition/information on ingredients**General chemical description:**

Lubricant

Declaration of the ingredients according to CLP (EC) No 1272/2008:

Hazardous components CAS-No.	EC Number REACH-Reg No.	content	Classification
2,2'-Thiodiethylene bis(3-(3,5-di-tert-butyl-4-hydroxyphenyl)propionate) 41484-35-9	255-392-8 01-2119960149-32	< 2,5 %	Chronic hazards to the aquatic environment 4 H413

For full text of the H - statements and other abbreviations see section 16 "Other information".

Substances without classification may have community workplace exposure limits available.

Declaration of ingredients according to DPD (EC) No 1999/45:

Hazardous components CAS-No.	EC Number REACH-Reg No.	content	Classification
2,2'-Thiodiethylene bis(3-(3,5-di-tert-butyl-4-hydroxyphenyl)propionate) 41484-35-9	255-392-8 01-2119960149-32	< 2,5 %	R53

For full text of the R-Phrases indicated by codes see section 16 'Other Information'.

Substances without classification may have community workplace exposure limits available.

SECTION 4: First aid measures**4.1. Description of first aid measures**

Inhalation:

Move to fresh air. If symptoms persist, seek medical advice.

Skin contact:

Rinse with running water and soap.
Obtain medical attention if irritation persists.

Eye contact:

Rinse immediately with plenty of running water (for 10 minutes), seek medical attention from a specialist.

Ingestion:

Rinse mouth, drink 1-2 glasses of water, do not induce vomiting, consult a doctor.

4.2. Most important symptoms and effects, both acute and delayed

Prolonged or repeated contact may cause skin irritation.

Prolonged or repeated contact may cause eye irritation.

4.3. Indication of any immediate medical attention and special treatment needed

See section: Description of first aid measures

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable extinguishing media:

Carbon dioxide, foam, powder

5.2. Special hazards arising from the substance or mixture

In the event of a fire, carbon monoxide (CO), carbon dioxide (CO₂) and nitrogen oxides (NO_x) can be released.

5.3. Advice for firefighters

Wear self-contained breathing apparatus and full protective clothing, such as turn-out gear.

Additional information:

In case of fire, keep containers cool with water spray.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Avoid contact with skin and eyes.

Wear protective equipment.

Ensure adequate ventilation.

6.2. Environmental precautions

Do not let product enter drains.

6.3. Methods and material for containment and cleaning up

Scrape up spilled material and place in a closed container for disposal.

For small spills wipe up with paper towel and place in container for disposal.

6.4. Reference to other sections

See advice in section 8

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Avoid skin and eye contact.

Hygiene measures:

Wash hands before work breaks and after finishing work.

Do not eat, drink or smoke while working.

Good industrial hygiene practices should be observed.

7.2. Conditions for safe storage, including any incompatibilities

Store in a cool, well-ventilated place.

7.3. Specific end use(s)

Lubricating Oils

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

Occupational Exposure Limits

Valid for

Great Britain

None

Predicted No-Effect Concentration (PNEC):

Name on list	Environmental Compartment	Exposure period	Value				Remarks
			mg/l	ppm	mg/kg	others	
Thiodiethylene bis[3-(3,5-di-tert-butyl-4-hydroxyphenyl)propionate] 41484-35-9	STP					1 mg/L	

Derived No-Effect Level (DNEL):

Name on list	Application Area	Route of Exposure	Health Effect	Exposure Time	Value	Remarks
Thiodiethylene bis[3-(3,5-di-tert-butyl-4-hydroxyphenyl)propionate] 41484-35-9	worker	inhalation	Long term exposure - systemic effects		3 mg/m ³	
Thiodiethylene bis[3-(3,5-di-tert-butyl-4-hydroxyphenyl)propionate] 41484-35-9	worker	Dermal	Long term exposure - systemic effects		13,8 mg/kg bw/day	
Thiodiethylene bis[3-(3,5-di-tert-butyl-4-hydroxyphenyl)propionate] 41484-35-9	general population	Dermal	Long term exposure - systemic effects		6,9 mg/kg bw/day	
Thiodiethylene bis[3-(3,5-di-tert-butyl-4-hydroxyphenyl)propionate] 41484-35-9	general population	oral	Long term exposure - systemic effects		0,69 mg/kg bw/day	

Biological Exposure Indices:

None

8.2. Exposure controls:

Respiratory protection:

Ensure adequate ventilation.

An approved mask or respirator fitted with an organic vapour cartridge should be worn if the product is used in a poorly ventilated area

Filter type: A

Hand protection:

Chemical-resistant protective gloves (EN 374).

Suitable materials for short-term contact or splashes (recommended: at least protection index 2, corresponding to > 30 minutes permeation time as per EN 374):

nitrile rubber (NBR; \geq 0.4 mm thickness)

Suitable materials for longer, direct contact (recommended: protection index 6, corresponding to > 480 minutes permeation time as per EN 374):

nitrile rubber (NBR; \geq 0.4 mm thickness)

This information is based on literature references and on information provided by glove manufacturers, or is derived by analogy with similar substances. Please note that in practice the working life of chemical-resistant protective gloves may be considerably shorter than the permeation time determined in accordance with EN 374 as a result of the many influencing factors (e.g. temperature). If signs of wear and tear are noticed then the gloves should be replaced.

Eye protection:

Safety glasses with sideshields or chemical safety goggles should be worn if there is a risk of splashing.

Skin protection:

Wear suitable protective clothing.

SECTION 9: Physical and chemical properties**9.1. Information on basic physical and chemical properties**

Appearance

liquid

Milky white

Odor

None

Odour threshold

No data available / Not applicable

pH	not applicable
Initial boiling point	Not determined
Flash point	> 220 °C (> 428 °F); Cleveland open cup
Decomposition temperature	No data available / Not applicable
Vapour pressure	No data available / Not applicable
Density	0,89 g/cm ³
()	
Bulk density	No data available / Not applicable
Viscosity	No data available / Not applicable
Viscosity (kinematic)	No data available / Not applicable
Explosive properties	No data available / Not applicable
Solubility (qualitative)	Insoluble
Solidification temperature	No data available / Not applicable
Melting point	No data available / Not applicable
Flammability	No data available / Not applicable
Auto-ignition temperature	No data available / Not applicable
Explosive limits	No data available / Not applicable
Partition coefficient: n-octanol/water	No data available / Not applicable
Evaporation rate	No data available / Not applicable
Vapor density	No data available / Not applicable
Oxidising properties	No data available / Not applicable

9.2. Other information

No data available / Not applicable

SECTION 10: Stability and reactivity

10.1. Reactivity

Strong oxidizing agents.

10.2. Chemical stability

Stable under recommended storage conditions.

10.3. Possibility of hazardous reactions

See section reactivity

10.4. Conditions to avoid

No decomposition if used according to specifications.

10.5. Incompatible materials

See section reactivity

10.6. Hazardous decomposition products

carbon monoxide

SECTION 11: Toxicological information

11.1. Information on toxicological effects

General toxicological information:

The mixture is classified based on the available hazard information for the ingredients as defined in the classification criteria for mixtures for each hazard class or differentiation in Annex I to Regulation 1272/2008/EC. Relevant available health/ecological information for the substances listed under Section 3 is provided in the following.

Oral toxicity:

This material is considered to have low toxicity if swallowed.

Inhalative toxicity:

Due to the low volatility of the product there are no hazards associated with inhalation under normal conditions of use

Skin irritation:

Prolonged or repeated contact may cause skin irritation.

Eye irritation:

Prolonged or repeated contact may cause eye irritation.

Acute oral toxicity:

Hazardous components CAS-No.	Value type	Value	Route of application	Exposure time	Species	Method
2,2'-Thiodiethylene bis(3-(3,5-di-tert-butyl-4-hydroxyphenyl)propionate) 41484-35-9	LD50	> 2.000 mg/kg	oral		rat	

Acute inhalative toxicity:

Hazardous components CAS-No.	Value type	Value	Route of application	Exposure time	Species	Method

Acute dermal toxicity:

Hazardous components CAS-No.	Value type	Value	Route of application	Exposure time	Species	Method

SECTION 12: Ecological information

General ecological information:

The mixture is classified based on the available hazard information for the ingredients as defined in the classification criteria for mixtures for each hazard class or differentiation in Annex I to Regulation 1272/2008/EC. Relevant available health/ecological information for the substances listed under Section 3 is provided in the following.

12.1. Toxicity**Ecotoxicity:**

Do not empty into drains / surface water / ground water.

Hazardous components CAS-No.	Value type	Value	Acute Toxicity Study	Exposure time	Species	Method

12.2. Persistence and degradability**Persistence and Biodegradability:**

The product is not biodegradable.

12.3. Bioaccumulative potential / 12.4. Mobility in soil**Mobility:**

Cured adhesives are immobile.

Bioaccumulative potential:

No data available.

Hazardous components CAS-No.	LogKow	Bioconcentration factor (BCF)	Exposure time	Species	Temperature	Method
2,2'-Thiodiethylene bis(3-(3,5-di-tert-butyl-4-hydroxyphenyl)propionate) 41484-35-9	> 6					

12.5. Results of PBT and vPvB assessment

Hazardous components CAS-No.	PBT/vPvB

2,2'-Thiodiethylene bis(3-(3,5-di-tert-butyl-4-hydroxyphenyl)propionate)
41484-35-9

Not fulfilling Persistent, Bioaccumulative and Toxic (PBT), very Persistent and very Bioaccumulative (vPvB) criteria.

12.6. Other adverse effects

No data available.

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Product disposal:

Dispose of in accordance with local and national regulations.

Disposal of uncleaned packages:

After use, tubes, cartons and bottles containing residual product should be disposed of as chemically contaminated waste in an authorised legal land fill site or incinerated.

Disposal must be made according to official regulations.

Waste code

The valid EWC waste code numbers are source-related. The manufacturer is therefore unable to specify EWC waste codes for the articles or products used in the various sectors. The EWC codes listed are intended as a recommendation for users. We will be happy to advise you.

08 04 09 waste adhesives and sealants containing organic solvents and other dangerous substances

SECTION 14: Transport information

14.1. UN number

Not hazardous according to RID, ADR, ADNR, IMDG, IATA-DGR.

14.2. UN proper shipping name

Not hazardous according to RID, ADR, ADNR, IMDG, IATA-DGR.

14.3. Transport hazard class(es)

Not hazardous according to RID, ADR, ADNR, IMDG, IATA-DGR.

14.4. Packaging group

Not hazardous according to RID, ADR, ADNR, IMDG, IATA-DGR.

14.5. Environmental hazards

Not hazardous according to RID, ADR, ADNR, IMDG, IATA-DGR.

14.6. Special precautions for user

Not hazardous according to RID, ADR, ADNR, IMDG, IATA-DGR.

14.7. Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code

not applicable

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

VOC content
(1999/13/EC) 0 %

15.2. Chemical safety assessment

A chemical safety assessment has not been carried out.

SECTION 16: Other information

The labelling of the product is indicated in Section 2. The full text of all abbreviations indicated by codes in this safety data sheet are as follows:

R53 May cause long-term adverse effects in the aquatic environment.

H413 May cause long lasting harmful effects to aquatic life.

Further information:

This information is based on our current level of knowledge and relates to the product in the state in which it is delivered. It is intended to describe our products from the point of view of safety requirements and is not intended to guarantee any particular properties.