




## **QU1604 Size: 9V** (6LR61)

Alkaline-Manganese Dioxide Battery

DURACELL	
Nominal voltage	9 V
Impedance	1,700 m-ohm @ 1 kHz
Typical weight	46 g (1.6 oz)
Typical volume	22.8 cm <sup>3</sup> (1.4 in <sup>3</sup> )
Terminals	Miniature snap
Storage temperature range	5°C to 30°C (41°F to 86°F)
Operating temperature range	-20°C to 54°C (-4°F to 130°F)
Designation	<b>ANSI:</b> 1604A <b>IEC:</b> 6LR61







## **DURACELL**BATTERIES

Berkshire Corporate Park Bethel, CT. 06801 U.S.A.

Telephone: Toll-free 1-800-544-5454


www.duracell.com


Delivered capacity is dependent on the applied load, operating temperature and cut-off voltage. Please refer to the charts and discharge data shown for examples of the energy/service life that the battery will provide for various load conditions.





## **QU1604 Size: 9V** (6LR61)

Alkaline-Manganese Dioxide Battery









## DURACELL®

Berkshire Corporate Park Bethel, CT. 06801 U.S.A.

Telephone: Toll-free 1-800-544-5454

www.duracell.com

Delivered capacity is dependent on the applied load, operating temperature and cut-off voltage. Please refer to the charts and discharge data shown for examples of the energy/service life that the battery will provide for various load conditions.