



# LIMIT & SAFETY SWITCHES

## 50mm Wide IP66 Limit Switches

- 50mm width
- IP66 metal casing
- Snap action contacts
- Other types available
-   approved

CE 21



### SPECIFICATION

Rating	500V
Shock withstand	50g
Impulse withstand voltage	6kV
Working temperature	-25°C to +70°C
Switching frequency	3600 cycles/h
Load factor	0.5
Short circuit protection	10A gG fuse

IP66 METAL CASING	PLUNGER TYPE	MAX ACTUATION SPEED	ACTUATION/ NC OPERATION
CE21.00.AM	Plain Plunger	0.5ms <sup>-1</sup>	15N/30N
CE21.00.BM	Steel Roller Plunger	0.3ms <sup>-1</sup>	12N/30N
CE21.00.HM	Adjustable Rod Lever	1.5ms <sup>-1</sup>	0.10Nm/0.32Nm
CE21.00.GM	Adjustable Rod Lever	1.5ms <sup>-1</sup>	0.10Nm/0.32Nm
CE21.00.EM	Nylon Roller Lever	1.5ms <sup>-1</sup>	0.10Nm/0.32Nm
CE21.00.EM/50	Rubber Roller Lever	1.5ms <sup>-1</sup>	0.10Nm/0.32Nm
CE21.00.FM	Adjustable Roller Lever	1.5ms <sup>-1</sup>	0.10Nm/0.32Nm
CE21.00.FM/50	Adjustable Rubber Roller Lever	1.5ms <sup>-1</sup>	0.10Nm/0.32Nm
CE21.00.HLTM	Nylon Actuator with Stainless Steel Spring	1.5ms <sup>-1</sup>	0.10Nm/-
CE21.00.FRM/50	Adjustable Lever with Adjustable Rubber Roller	1.0ms <sup>-1</sup>	0.10Nm/-
CE21.00.IM	Nylon Roller Lever	1.0ms <sup>-1</sup>	0.10Nm/0.32Nm

