





Main

Range	TeSys
Product name	TeSys F
Product or component type	Contacteur
Device short name	LC1F
Contacteur application	Resistive load
Utilisation category	AC-1
Poles description	4P
Power pole contact composition	4 NO
[Ue] rated operational voltage	<= 460 V DC <= 1000 V AC 50/60 Hz
[Ie] rated operational current	200 A (<= 40 °C) at <= 440 V AC AC-1
[Uimp] rated impulse withstand voltage	8 kV
Overtoltage category	III
[Ith] conventional free air thermal current	200 A at <= 40 °C
Irms rated making capacity	1150 A AC conforming to IEC 60947-4-1
Rated breaking capacity	920 kA conforming to IEC 60947-4-1
[Icw] rated short-time withstand current	320 A <= 40 °C 10 min 400 A <= 40 °C 3 min 520 A <= 40 °C 1 min 640 A <= 40 °C 30 s 1100 A <= 40 °C 10 s
Associated fuse rating	200 A gG at <= 440 V 125 A aM at <= 440 V
Average impedance	0.37 mOhm at 50 Hz - Ith 200 A
[Ui] rated insulation voltage	1500 V conforming to VDE 0110 group C 1000 V conforming to IEC 60947-4-1
Power dissipation per pole	15 W AC-1
Mounting support	Plate
Standards	EN 60947-1 EN 60947-4-1 IEC 60947-1 IEC 60947-4-1 JEM 1038
Product certifications	BV CCC CSA DNV GL RINA RMRoS UL LROS

Connections - terminals	Power circuit : bar 2 x (20 x 3 mm) Control circuit : screw clamp terminals 2 cable(s) 1...4 mm ² - cable stiffness: solid - without cable end Control circuit : screw clamp terminals 1 cable(s) 1...4 mm ² - cable stiffness: solid - without cable end Control circuit : screw clamp terminals 2 cable(s) 1...2.5 mm ² - cable stiffness: flexible - with cable end Control circuit : screw clamp terminals 1 cable(s) 1...4 mm ² - cable stiffness: flexible - with cable end Control circuit : screw clamp terminals 2 cable(s) 1...4 mm ² - cable stiffness: flexible - without cable end Control circuit : screw clamp terminals 1 cable(s) 1...4 mm ² - cable stiffness: flexible - without cable end Power circuit : connector 1 cable(s) 95 mm ² Power circuit : lugs-ring terminals 1 cable(s) 95 mm ²
Tightening torque	Control circuit : 1.2 N.m Power circuit : 10 N.m

Environment

IP degree of protection	IP2x front face with shrouds (ordered separately) conforming to VDE 0106 IP2x front face with shrouds (ordered separately) conforming to IEC 60529
Protective treatment	TH
Ambient air temperature for operation	-5...55 °C
Ambient air temperature for storage	-60...80 °C
Permissible ambient air temperature around the device	-40...70 °C
Operating altitude	3000 m without derating in temperature
Mechanical robustness	Shocks contactor closed 15 Gn for 11 ms Shocks contactor open 9 Gn for 11 ms Vibrations contactor closed 6 Gn, 5...300 Hz Vibrations contactor open 2 Gn, 5...300 Hz
Height	162 mm
Width	200.5 mm
Depth	171 mm
Product weight	3.83 kg

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS	Compliant - since 0852 - Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available Download Product Environmental
Product end of life instructions	Available Download End Of Life Manual