

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

172160-1803

Status:

Active

Overview:

KK® Interconnect System - Molex

Description:

3.96mm Pitch KK® Crimp Terminal, Phosphor Bronze, Tin (Sn), Bifurcated, 18-20 AWG, Reel



Documents:

Drawing (PDF)

Product Specification PS-172160-0001 (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	Crimp Terminals
Series	172160
Application	Power
Crimp Quality Equipment	Yes
Overview	KK® Interconnect System - Molex
Product Name	KK®
UPC	887191570068
Physical	
Durability (mating cycles max)	25
Gender	Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.172/g
Packaging Type	Reel
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	2.79mm max.
Wire Size AWG	18, 20
Wire Size mm²	N/A
Electrical	
Current - Maximum per Contact	7A
Material Info	
Reference - Drawing Numbers	
Product Specification	PS-172160-0001
Sales Drawing	SD-172160-0000

EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Contains SVHC: No

Low-Halogen Status

Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

172160Series

Use With

172159

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Hand Crimper	0638117500
Terminator Die	0011402096
Mini-Mac Applicator	0638885000

for KK® and Trifurcon™ Crimp Terminals

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION