




EEG.0K.303.CLN

MECHANICAL DETAILS

Shell Style Model	EE* : Fixed receptacle nut fixing with straight contacts for printed circuit (back panel mounting)
Keying	1 key (alpha=0, plug: male contacts, receptacle: female contacts)
Housing Material	Brass (chrome plated) shell and collet nut, nickel plated brass latch sleeve and mid pieces
Cable Fixing	0 - 0 mm

Variant 2 :

		A	B	E	M	N	P	e
mm		18	18	3.4	3.5	17.6	7	M14x1.0
in.		0.71	0.71	0.13	0.14	0.69	0.28	



PERFORMANCE DETAIL

Insert	0K.303 : 3 Low Voltage
Insulator	L: PEEK
Specifications	
Contact Type:	Print (straight)
Max. Matings:	5000
Contact Dia.:	0.9 mm (0.035in)
R (max):	4.8 mOhm



OTHER CHARACTERISTICS

Endurance (Shell)	Endurance (Shell):
Temp (min)	-55°C
Temp (max)	+200°C
Humidity (max):	<=95% [at 60 deg C /140 F]
Vibration:	15 g [10 Hz - 2000 Hz]
Shock Resistance:	100 g [6 ms]
Salt Spray	>144 hr
Climatical	50/175/21
Shielding (min):	95 dB (10 MHz)
Shielding (min):	80 dB (1 GHz)
IP Rating	68

