



HEP.3F.330.XLNP

MECHANICAL DETAILS

Shell Style Model HE* : Fixed receptacle nut fixing for printed circuit (back panel mounting)


Keying 3 keys (beta=145, gamma=70, plug: male contacts, receptacle: female contacts)

Housing Material Environment friendly aluminium (nickel plated, anthracite color) shell and nut, other pieces bronze/brass

Cable Fixing 0 - 0 mm

Variant 2 P : Watertight

	A	B	H	L
Mm.	22	23	11.43	21.6
In.	0.87	0.91	0.45	0.85



PERFORMANCE DETAIL

Insert 3F.330 : 30 Low Voltage

Insulator L: PEEK

Specifications

Contact Type: Print (straight)

Max. Matings: 5000

Contact Dia.: 0.7 mm (0.028in)

R (max): 6.1 mOhm

OTHER CHARACTERISTICS

Endurance (Shell) Endurance (Shell):

Temp (min) -15°C

Temp (max) +100°C

Humidity (max): <=95% [at 60 deg C /140 F]

Vibration: 15 g [10 Hz - 2000 Hz]

Shock Resistance: 100 g [6 ms]

Climatical 15/200/21 (Aluminium shell)

Pressure 5 bars

IP Rating 68

