

CGA4J3X7R1E684K125AB

TDK Item Description : CGA4J3X7R1E684KT***




Equivalent C2012X7R1E684K for Automotive

Application & Main Feature


Automotive Grade (General (Up to 50V))

Series

CGA4(2012) [EIA CC0805]



DC Bias Characteristic



Dimensions

L 2.00mm +/-0.2mm
W 1.25mm +/-0.2mm
T 1.25mm +/-0.2mm
B 0.20mm Min.
G 0.50mm Min.

Temperature Characteristic

X7R (-55 to 125 degC +/-15%)

Rated Voltage

1E (25Vdc)

Capacitance

680nF

Capacitance Tolerance

K (+/-10%)

Dissipation Factor

5% Max.


Insulation Resistance

735Mohm Min.


AEC-Q200

Yes


|Z|, ESR vs. Freq. Characteristics




Temperature Characteristic



Cap. vs. Freq. Characteristic



Ripple Temperature Rise Characteristic



All specifications are subject to change without notice.

September 28, 2013