

**Kit P/N:GRM-KIT-HICAP-E [0201~1210 Class 2 Hi Cap series]**

52

No.	Murata Global P/N	Size (EIA)	TC	WV	Cap.	Cap. Tol.	QTY
1	GRM033R60J105MEA2	0201	X5R	6.3V	1 $\mu$ F	$\pm$ 20%	100
2	GRM033R60J225ME47	0201	X5R	6.3V	2.2 $\mu$ F	$\pm$ 20%	100
3	GRM153R61A105ME95	0402	X5R	10V	1 $\mu$ F	$\pm$ 20%	20
4	GRM155R61A105KE01	0402	X5R	10V	1 $\mu$ F	$\pm$ 10%	100
5	GRM155R61C105KE01	0402	X5R	16V	1 $\mu$ F	$\pm$ 10%	100
6	GRM155R61E105KA12	0402	X5R	25V	1 $\mu$ F	$\pm$ 10%	100
7	GRM155R6YA105KE11	0402	X5R	35V	1 $\mu$ F	$\pm$ 10%	20
8	GRM155R60J225KE95	0402	X5R	6.3V	2.2 $\mu$ F	$\pm$ 10%	20
9	GRM155R61A225KE95	0402	X5R	10V	2.2 $\mu$ F	$\pm$ 10%	20
10	GRM155R61C225KE44	0402	X5R	16V	2.2 $\mu$ F	$\pm$ 10%	20
11	GRM155R61E225KE11	0402	X5R	25V	2.2 $\mu$ F	$\pm$ 10%	20
12	GRM155R60J475ME47	0402	X5R	6.3V	4.7 $\mu$ F	$\pm$ 20%	100
13	GRM155R61A475MEAA	0402	X5R	10V	4.7 $\mu$ F	$\pm$ 20%	20
14	GRM155R60J106ME15	0402	X5R	6.3V	10 $\mu$ F	$\pm$ 20%	100
15	GRM185R61C105KE44	0603	X5R	16V	1 $\mu$ F	$\pm$ 10%	20
16	GRM185R61E105KA12	0603	X5R	25V	1 $\mu$ F	$\pm$ 10%	20
17	GRM188R61H105KAAL	0603	X5R	50V	1 $\mu$ F	$\pm$ 10%	20
18	GRM188R61H225KE11	0603	X5R	50V	2.2 $\mu$ F	$\pm$ 10%	20
19	GRM185R61A475KE11	0603	X5R	10V	4.7 $\mu$ F	$\pm$ 10%	20
20	GRM185R61C475KE11	0603	X5R	16V	4.7 $\mu$ F	$\pm$ 10%	20
21	GRM188R61C475KAAJ	0603	X5R	16V	4.7 $\mu$ F	$\pm$ 10%	20
22	GRM188R61E475KE11	0603	X5R	25V	4.7 $\mu$ F	$\pm$ 10%	20
23	GRM188R6YA475KE15	0603	X5R	35V	4.7 $\mu$ F	$\pm$ 10%	20
24	GRM185R60J106ME15	0603	X5R	6.3V	10 $\mu$ F	$\pm$ 20%	20
25	GRM188R60J106ME47	0603	X5R	6.3V	10 $\mu$ F	$\pm$ 20%	100
26	GRM188R61A106KE69	0603	X5R	10V	10 $\mu$ F	$\pm$ 10%	20
27	GRM188R61C106KAAL	0603	X5R	16V	10 $\mu$ F	$\pm$ 10%	20
28	GRM188R61E106MA73	0603	X5R	25V	10 $\mu$ F	$\pm$ 20%	100
29	GRM188R60J226MEA0	0603	X5R	6.3V	22 $\mu$ F	$\pm$ 20%	100
30	GRM188R61A226ME15	0603	X5R	10V	22 $\mu$ F	$\pm$ 20%	20
31	GRM188R60J476ME15	0603	X5R	6.3V	47 $\mu$ F	$\pm$ 20%	20
32	GRM21BR61H475KE51	0805	X5R	50V	4.7 $\mu$ F	$\pm$ 10%	20
33	GRM219R61E106KA12	0805	X5R	25V	10 $\mu$ F	$\pm$ 10%	20
34	GRM21BR61E106KA73	0805	X5R	25V	10 $\mu$ F	$\pm$ 10%	100
35	GRM21BR6YA106KE43	0805	X5R	35V	10 $\mu$ F	$\pm$ 10%	20
36	GRM21BR60J226ME39	0805	X5R	6.3V	22 $\mu$ F	$\pm$ 20%	20
37	GRM219R61A226MEA0	0805	X5R	10V	22 $\mu$ F	$\pm$ 20%	20
38	GRM21BR61A226ME51	0805	X5R	10V	22 $\mu$ F	$\pm$ 20%	20
39	GRM219R61C226ME15	0805	X5R	16V	22 $\mu$ F	$\pm$ 20%	20
40	GRM21BR61C226ME44	0805	X5R	16V	22 $\mu$ F	$\pm$ 20%	20
41	GRM21BR61E226ME44	0805	X5R	25V	22 $\mu$ F	$\pm$ 20%	20
42	GRM219R60J476ME44	0805	X5R	6.3V	47 $\mu$ F	$\pm$ 20%	20
43	GRM21BR60J476ME15	0805	X5R	6.3V	47 $\mu$ F	$\pm$ 20%	20

44	GRM21BR61A476ME15	0805	X5R	10V	47μF	±20%	20
45	GRM21BR60G107ME15	0805	X5R	4V	100μF	±20%	20
46	GRM31CR61H106KA12	1206	X5R	50V	10μF	±10%	20
47	GRM31CR61E226ME15	1206	X5R	25V	22μF	±20%	20
48	GRM31CR61A476ME15	1206	X5R	10V	47μF	±20%	20
49	GRM31CR60J107ME39	1206	X5R	6.3V	100μF	±20%	20
50	GRM32ER71H106KA12	1210	X7R	50V	10μF	±10%	20
51	GRM32ER61C476ME15	1210	X5R	16V	47μF	±20%	20
52	GRM32ER61A107ME20	1210	X5R	10V	100μF	±20%	20