



Pneumatic Hand Tool
T&B Catalog Number:

ERG50P

UPC Number:

78620989207

Status:

Active

Description:

Pneumatic Hand Tool for Nylon Cable Ties 18-50 lbs. - .094-.184 cable tie width, includes 9-ft. air hose

Features

Pneumatic power combined with ergonomic design enables you to tension and trim large quantities in rapid succession with accuracy and one-button ease. 360 degree rotating nose maximizes flexibility in tight spaces - no twisting required. Front-access tension-adjustment wheel permits fast, easy changes.

Application

Cable Tie installation.

General

For Cable Ties	18 to 50 lbs.
Tooling Functionality	Fastening
For Tie Width (inches)	.094 - .184

Specifications

Tension Setting	Adjustable
Cutting Mechanism	Automatic
Operating Pressure (psi)	85-100 psi (non-lubricated air)

Tooling

Tool Service Site	Available on Website
-------------------	----------------------

Packaging

T&B Inner Pack	1
Package in Units	5
T&B Sold in UOM	Each
T&B Weight Per UOM	1.92 lbs. Each

Application Support

T&B Sales Drawings	wsd-000415
Overview	Available on Website

Certifications

RoHS Compliance	Yes
-----------------	-----

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
 www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email:techsupport@tnb.com