



## **N** Fitting-Tools

Packing unit: in plastic tubes of 1

Nominal thread size	Pitch mm	Ø <sub>1</sub> mm	L <sub>1</sub> mm	Article no.
M 3	0,50	2,0	60,0	244 183
M 4	0,70	2,8	60,0	244 184
M 5	0,80	3,5	60,0	244 185
M 6	1,00	4,8	60,0	244 186
M 8	1,25	6,0	80,0	244 188
M 10	1,50	7,5	80,0	244 190
M 12	1,75	9,5	80,0	244 192
M 14	2,00	11,2	80,0	244 194

## **N** ProCoil Thread repairing assortment in steel case

45-piece set of ProCoil thread repairing tools



244 208



244 209

	Description	Article no.
Assortment 1	Assortment M 5 - M12 5 twist drills HSS Ø 5,2 - 6,2 - 8,3 - 10,3 - 12,4 mm + 5 single-cut taps DIN 352 HSS M 5 - M 6 - M 8 - M 10 - M 12 + 5 fitting tools M 5 - M 6 - M 8 - M 10 - M 12 + 5 pin-Breakers Ø 3,5 - 4,8 - 6,0 - 7,5 - 9,5 mm + 20 inserts M 5 - M 10: Height = 1,0 x Ø + 5 inserts M 12: Height = 1,0 x Ø	244 208
Assortment 2	Assortment M 6 - M14 5 twist drills HSS Ø 6,2 - 8,3 - 10,3 - 12,4 - 14,5 mm + 5 single-cut taps DIN 352 HSS M 6 - M 8 - M 10 - M 12 - M 14 + 5 fitting tools M 6 - M 8 - M 10 - M 12 - M 14 + 5 pin-Breakers Ø 4,8 - 6,0 - 7,5 - 9,5 - 11,2 mm + 20 inserts M 6 - M 12: Height = 1,0 x Ø + 5 inserts M 14: Height = 1,0 x Ø	244 209

