


Capacitor, Tantalum, 220 uF, +/-20% Tol, 10 V



Dimensions (mm)		
Symbol	Dimension	Tolerance
D	8.92	+/-0.25
L	19.96	+/-0.79
L2	23.42	
F	0.64	+/-0.05
LL	38.10	+/-6.35

Notes:

- Dimensions include insulating sleeve (standard)
- When supplied on T&R or AMMO, lead length is determined by taping specification.

General Information

Supplier:	KEMET
Application:	General Purpose
Body Type:	Axial Hermetic ('cs13-style')
Lead Type:	Un-insulated Wire
Termination Type:	Tin (Sn)
RoHS:	Yes

Specifications

Capacitance:	220 uF
Tolerance:	+/-20%
Voltage:	10 V (85C)
Voltage:	9 V (125C Surge)
Voltage:	0.1 V (125C Reverse)
Temperature Range:	-55/+125C
Resistance/ESR:	0.6 Ohms (100kHz)
Leakage Current:	10 uA
Dissipation Factor:	8%

Packaging Specifications

Package Kind:	Bulk
Package Type:	Bag
Package Quantity:	20